

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P264800

Luminaire Tested: **LD2B05D010 EU2B0510SP158050 2LBDL*WH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P264800
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1711-432-2)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B05D010 EU2B0510SP158050 2LBDL*WH
Description: 500 Lumen, 2inch Portfolio LED Downlight
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 780.0 lumens
Efficiency: N/A
Efficacy: 106.9 lumens/watt
Spacing Criteria (0/90/45): 0.31 / 0.31 / 0.32
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P264800

CATALOG NUMBER: LD2B05D010 EU2B0510SP158050 2LBDL*WH

Luminous Intensity Polar Plot





TEST NUMBER: P264800

CATALOG NUMBER: LD2B05D010 EU2B0510SP158050 2LBDL*WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	115	113	111	110	113	111	110	108	107	106	105	104	103	102	100	99	99	97				97															
2	112	108	106	103	110	107	104	102	104	102	100	101	99	98	98	97	96	94				94															
3	109	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	92				92															
4	105	100	97	94	104	99	96	93	97	95	92	96	93	91	94	92	90	89				89															
5	103	97	93	91	101	96	93	90	95	92	89	93	91	89	92	90	88	87				87															
6	100	94	90	88	99	94	90	87	92	89	87	91	88	86	90	88	86	85				85															
7	98	92	88	85	97	91	88	85	90	87	85	89	86	84	88	86	84	83				83															
8	95	89	86	83	94	89	85	83	88	85	82	87	84	82	86	84	82	81				81															
9	93	87	83	81	92	87	83	81	86	83	81	85	82	80	85	82	80	79				79															
10	91	85	82	79	91	85	81	79	84	81	79	84	81	79	83	80	78	78				78															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2753551
5°	2241138
10°	1210601
15°	482674
20°	193524
25°	92705
30°	48081
35°	25416
40°	14104
45°	8721
50°	5987
55°	4043
60°	3059
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P264800

CATALOG NUMBER: LD2B05D010 EU2B0510SP158050 2LBDL*WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	363.9	46.7
10°-20°	287.1	36.8
20°-30°	84.7	10.9
30°-40°	28.2	3.6
40°-50°	10.6	1.4
50°-60°	4.7	0.6
60°-70°	0.8	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	735.8	94.3
0°-40°	764.0	97.9
0°-60°	779.3	99.9
0°-90°	780.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	780.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5581	
5°	4525	364
15°	945	287
25°	170	85
35°	42	28
45°	12	11
55°	5	5
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P264800

CATALOG NUMBER: LD2B05D010 EU2B0510SP158050 2LBDL*WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	5581.2
2.5°	5356.3
5°	4525.3
7.5°	3486.5
10°	2416.5
12.5°	1546.4
15°	945.0
17.5°	576.4
20°	368.6
22.5°	246.8
25°	170.3
27.5°	120.3
30°	84.4
32.5°	59.4
35°	42.2
37.5°	29.7
40°	21.9
42.5°	17.2
45°	12.5
47.5°	10.9
50°	7.8
52.5°	6.2
55°	4.7
57.5°	4.7
60°	3.1
62.5°	1.6
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)