

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P496242

Luminaire Tested: **LDA2B109035R45D010 2LBDLC1MMS**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P496242  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-42)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B109035R45D010 2LBDLC1MMS  
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 3500K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 914.4 lumens  
Efficiency: N/A  
Efficacy: 91.4 lumens/watt  
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.65  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P496242

CATALOG NUMBER: LDA2B109035R45D010 2LBDLC1MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P496242

CATALOG NUMBER: LDA2B109035R45D010 2LBDLC1MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95
2	110	105	102	99	108	104	101	98	101	98	96	98	96	94	95	93	92	90
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86
4	101	95	90	86	99	94	89	86	91	88	85	90	86	84	88	85	83	82
5	97	90	85	81	95	89	84	81	87	83	80	86	82	80	84	81	79	78
6	93	86	81	77	92	85	80	77	84	79	76	82	79	76	81	78	75	74
7	90	82	77	73	88	81	76	73	80	76	73	79	75	72	78	74	72	71
8	86	78	73	70	85	78	73	70	77	72	69	76	72	69	75	71	69	68
9	83	75	70	66	82	74	70	66	74	69	66	73	69	66	72	68	66	65
10	80	72	67	64	79	71	67	64	71	66	63	70	66	63	69	66	63	62

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	906256
5°	886293
10°	822297
15°	701230
20°	527965
25°	318290
30°	153473
35°	69564
40°	32009
45°	16536
50°	8750
55°	3269
60°	888
65°	584
70°	721
75°	0
80°	0
85°	0



TEST NUMBER: P496242

CATALOG NUMBER: LDA2B109035R45D010 2LBDLC1MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	166.4	18.2
10°-20°	374.9	41.0
20°-30°	267.9	29.3
30°-40°	80.3	8.8
40°-50°	19.9	2.2
50°-60°	4.2	0.5
60°-70°	0.6	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	809.2	88.5
0°-40°	889.4	97.3
0°-60°	913.5	99.9
0°-90°	914.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	914.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1837	
5°	1790	166
15°	1373	375
25°	585	268
35°	116	80
45°	24	20
55°	4	4
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P496242

CATALOG NUMBER: LDA2B109035R45D010 2LBDLC1MMS

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1836.9
1°	1840.2
2°	1836.0
3°	1820.3
4°	1809.0
5°	1789.6
6°	1770.1
7°	1749.3
8°	1715.2
9°	1683.0
10°	1641.4
11°	1599.7
12°	1547.2
13°	1490.8
14°	1438.3
15°	1372.9
16°	1309.0
17°	1236.6
18°	1167.9
19°	1083.7
20°	1005.6
21°	918.9
22.5°	789.7
23°	746.1
24°	661.4
25°	584.7
26°	508.0
27°	437.9
28°	372.6
29°	319.1
30°	269.4
32.5°	177.1
35°	115.5
37.5°	75.7
40°	49.7
42.5°	33.6
45°	23.7
47.5°	17.0
50°	11.4
52.5°	7.1
55°	3.8
57.5°	1.9
60°	0.9
62.5°	0.9
65°	0.5



TEST NUMBER: P496242

CATALOG NUMBER: LDA2B109035R45D010 2LBDLC1MMS

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.5
70°	0.5
72.5°	0.5
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)