

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P496278

Luminaire Tested: **LDA2B109035R65D010 2LBDL1GPH**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P496278  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-68)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B109035R65D010 2LBDL1GPH  
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 3500K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 828.0 lumens  
Efficiency: N/A  
Efficacy: 82.8 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.94  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P496278

CATALOG NUMBER: LDA2B109035R65D010 2LBDL1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P496278

CATALOG NUMBER: LDA2B109035R65D010 2LBDL1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	87
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80
4	97	89	83	79	95	88	83	79	86	81	78	84	80	77	82	78	76	74
5	92	83	77	73	90	82	76	72	80	75	72	79	74	71	77	73	70	69
6	87	78	72	67	85	77	71	67	75	70	66	74	69	66	73	69	65	64
7	82	73	67	62	81	72	66	62	71	66	62	70	65	61	68	64	61	60
8	78	68	62	58	77	68	62	58	67	61	58	66	61	57	65	60	57	56
9	74	64	58	54	73	64	58	54	63	58	54	62	57	54	61	57	53	52
10	71	61	55	51	70	60	54	51	59	54	50	59	54	50	58	53	50	49

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	433221
5°	415165
10°	395368
15°	375770
20°	349561
25°	322699
30°	280000
35°	200922
40°	109100
45°	46608
50°	20033
55°	7225
60°	1283
65°	1051
70°	577
75°	0
80°	0
85°	0



TEST NUMBER: P496278

CATALOG NUMBER: LDA2B109035R65D010 2LBDL1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	78.5	9.5
10°-20°	206.1	24.9
20°-30°	269.4	32.5
30°-40°	205.0	24.8
40°-50°	59.3	7.2
50°-60°	8.9	1.1
60°-70°	0.8	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	554.0	66.9
0°-40°	759.0	91.7
0°-60°	827.1	99.9
0°-90°	828.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	828.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	878	
5°	838	78
15°	736	206
25°	593	269
35°	334	205
45°	67	59
55°	8	9
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P496278

CATALOG NUMBER: LDA2B109035R65D010 2LBDL1GPH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	878.1
1°	875.0
2°	870.2
3°	860.4
4°	849.8
5°	838.3
6°	827.3
7°	817.5
8°	808.2
9°	799.8
10°	789.2
11°	779.9
12°	770.2
13°	760.5
14°	749.8
15°	735.7
16°	725.1
17°	712.2
18°	692.8
19°	682.6
20°	665.8
21°	650.7
22.5°	627.7
23°	618.9
24°	605.2
25°	592.8
26°	576.4
27°	558.3
28°	538.4
29°	517.1
30°	491.5
32.5°	421.1
35°	333.6
37.5°	246.0
40°	169.4
42.5°	107.5
45°	66.8
47.5°	41.6
50°	26.1
52.5°	15.5
55°	8.4
57.5°	3.1
60°	1.3
62.5°	0.9
65°	0.9



TEST NUMBER: P496278

CATALOG NUMBER: LDA2B109035R65D010 2LBDL1GPH

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)