

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P496297

Luminaire Tested: **LDA2B109035R70D010 2LBD1WH**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P496297
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-79)
Test Lab: INNOVATION CENTER
Issue Date: 3/8/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B109035R70D010 2LBD1WH
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 3500K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 867.4 lumens
Efficiency: N/A
Efficacy: 86.7 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.09
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 10
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P496297

CATALOG NUMBER: LDA2B109035R70D010 2LBD1WH

Luminous Intensity Polar Plot





TEST NUMBER: P496297

CATALOG NUMBER: LDA2B109035R70D010 2LBD1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	85	82	80	78
4	95	87	81	77	93	86	81	76	84	79	75	82	78	74	80	76	74	72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61
7	80	70	63	59	79	69	63	59	68	62	58	67	62	58	66	61	58	56
8	76	65	59	54	74	65	59	54	64	58	54	62	57	54	61	57	54	52
9	71	61	55	50	70	61	54	50	60	54	50	59	54	50	58	53	50	48
10	68	57	51	47	67	57	51	47	56	50	47	55	50	46	54	50	46	45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	338940
5°	335183
10°	333548
15°	332355
20°	320528
25°	307294
30°	304212
35°	259765
40°	162104
45°	75005
50°	27171
55°	1892
60°	888
65°	1051
70°	577
75°	762
80°	0
85°	0



TEST NUMBER: P496297

CATALOG NUMBER: LDA2B109035R70D010 2LBD1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	64.2	7.4
10°-20°	182.3	21.0
20°-30°	262.1	30.2
30°-40°	258.3	29.8
40°-50°	92.0	10.6
50°-60°	7.6	0.9
60°-70°	0.7	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	508.5	58.6
0°-40°	766.8	88.4
0°-60°	866.5	99.9
0°-90°	867.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	867.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	687	
5°	677	64
15°	651	182
25°	564	262
35°	431	258
45°	108	92
55°	2	8
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P496297

CATALOG NUMBER: LDA2B109035R70D010 2LBD1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	687.0
1°	687.0
2°	685.7
3°	686.1
4°	680.4
5°	676.8
6°	672.0
7°	670.2
8°	668.0
9°	667.6
10°	665.8
11°	663.6
12°	663.6
13°	659.6
14°	654.3
15°	650.7
16°	643.7
17°	639.7
18°	627.3
19°	618.9
20°	610.5
21°	599.4
22.5°	583.9
23°	577.7
24°	572.0
25°	564.5
26°	560.1
27°	552.5
28°	551.6
29°	543.7
30°	534.0
32.5°	496.4
35°	431.3
37.5°	346.8
40°	251.7
42.5°	172.1
45°	107.5
47.5°	64.1
50°	35.4
52.5°	13.3
55°	2.2
57.5°	1.3
60°	0.9
62.5°	0.9
65°	0.9



TEST NUMBER: P496297

CATALOG NUMBER: LDA2B109035R70D010 2LBD1WH

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.4
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)