

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P265115

Luminaire Tested: **LD2B05D010 EU2B0510SP159050 2LBLC\*MB**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P265115  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1711-432-2)  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD2B05D010 EU2B0510SP159050 2LBLC\*MB  
Description: 500 Lumen, 2inch Portfolio LED Downlight  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 566.0 lumens  
Efficiency: N/A  
Efficacy: 77.5 lumens/watt  
Spacing Criteria (0/90/45): 0.31 / 0.31 / 0.32  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 7.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P265115

CATALOG NUMBER: LD2B05D010 EU2B0510SP159050 2LBLC\*MB

### Luminous Intensity Polar Plot





TEST NUMBER: P265115

CATALOG NUMBER: LD2B05D010 EU2B0510SP159050 2LBLC\*MB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100													100															
1	115	113	111	110	113	111	110	108	107	106	105	104	103	102	100	99	99	97													97															
2	112	108	106	103	110	107	104	102	104	102	100	101	99	98	98	97	96	94													94															
3	109	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	92													92															
4	105	100	97	94	104	99	96	93	97	95	92	96	93	91	94	92	90	89													89															
5	103	97	93	91	101	96	93	90	95	92	89	93	91	89	92	90	88	87													87															
6	100	94	90	88	99	94	90	87	92	89	87	91	88	86	90	88	86	85													85															
7	98	92	88	85	97	91	88	85	90	87	85	89	86	84	88	86	84	83													83															
8	95	89	86	83	94	89	85	83	88	85	82	87	84	82	86	84	82	81													81															
9	93	87	83	81	92	87	83	81	86	83	81	85	82	80	85	82	80	79													79															
10	91	85	82	79	91	85	81	79	84	81	79	84	81	79	83	80	78	78													78															

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1998115
5°	1626240
10°	878456
15°	350283
20°	140444
25°	67283
30°	34865
35°	18430
40°	10240
45°	6349
50°	4375
55°	2925
60°	2269
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P265115

CATALOG NUMBER: LD2B05D010 EU2B0510SP159050 2LBLC\*MB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	264.1	46.7
10°-20°	208.4	36.8
20°-30°	61.5	10.9
30°-40°	20.5	3.6
40°-50°	7.7	1.4
50°-60°	3.4	0.6
60°-70°	0.5	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	533.9	94.3
0°-40°	554.4	97.9
0°-60°	565.5	99.9
0°-90°	566.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	566.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4050	
5°	3284	264
15°	686	208
25°	124	61
35°	31	20
45°	9	8
55°	3	3
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P265115

CATALOG NUMBER: LD2B05D010 EU2B0510SP159050 2LBLC\*MB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4050.0
2.5°	3886.7
5°	3283.7
7.5°	2529.9
10°	1753.5
12.5°	1122.2
15°	685.8
17.5°	418.3
20°	267.5
22.5°	179.1
25°	123.6
27.5°	87.3
30°	61.2
32.5°	43.1
35°	30.6
37.5°	21.5
40°	15.9
42.5°	12.5
45°	9.1
47.5°	7.9
50°	5.7
52.5°	4.5
55°	3.4
57.5°	3.4
60°	2.3
62.5°	1.1
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)