

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P496299

Luminaire Tested: **LDA2B109035R70D010 2LBD1WMH**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P496299  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-79)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/8/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B109035R70D010 2LBD1WMH  
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 3500K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 867.4 lumens  
Efficiency: N/A  
Efficacy: 86.7 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.09  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P496299

CATALOG NUMBER: LDA2B109035R70D010 2LBD1WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P496299

CATALOG NUMBER: LDA2B109035R70D010 2LBD1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97	96	95	93
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91	89	87	85
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		85	82	80	78
4	95	87	81	77	93	86	81	76	84	79	75		82	78	74		80	76	74	72
5	90	81	75	70	88	80	74	70	78	73	69		76	72	68		75	71	68	66
6	85	75	69	64	83	74	68	64	73	67	63		71	67	63		70	66	62	61
7	80	70	63	59	79	69	63	59	68	62	58		67	62	58		66	61	58	56
8	76	65	59	54	74	65	59	54	64	58	54		62	57	54		61	57	54	52
9	71	61	55	50	70	61	54	50	60	54	50		59	54	50		58	53	50	48
10	68	57	51	47	67	57	51	47	56	50	47		55	50	46		54	50	46	45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	338940
5°	335183
10°	333548
15°	332355
20°	320528
25°	307294
30°	304212
35°	259765
40°	162104
45°	75005
50°	27171
55°	1892
60°	888
65°	1051
70°	577
75°	762
80°	0
85°	0



TEST NUMBER: P496299

CATALOG NUMBER: LDA2B109035R70D010 2LBD1WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	64.2	7.4
10°-20°	182.3	21.0
20°-30°	262.1	30.2
30°-40°	258.3	29.8
40°-50°	92.0	10.6
50°-60°	7.6	0.9
60°-70°	0.7	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	508.5	58.6
0°-40°	766.8	88.4
0°-60°	866.5	99.9
0°-90°	867.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	867.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	687	
5°	677	64
15°	651	182
25°	564	262
35°	431	258
45°	108	92
55°	2	8
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P496299

CATALOG NUMBER: LDA2B109035R70D010 2LBD1WMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	687.0
1°	687.0
2°	685.7
3°	686.1
4°	680.4
5°	676.8
6°	672.0
7°	670.2
8°	668.0
9°	667.6
10°	665.8
11°	663.6
12°	663.6
13°	659.6
14°	654.3
15°	650.7
16°	643.7
17°	639.7
18°	627.3
19°	618.9
20°	610.5
21°	599.4
22.5°	583.9
23°	577.7
24°	572.0
25°	564.5
26°	560.1
27°	552.5
28°	551.6
29°	543.7
30°	534.0
32.5°	496.4
35°	431.3
37.5°	346.8
40°	251.7
42.5°	172.1
45°	107.5
47.5°	64.1
50°	35.4
52.5°	13.3
55°	2.2
57.5°	1.3
60°	0.9
62.5°	0.9
65°	0.9



TEST NUMBER: P496299

CATALOG NUMBER: LDA2B109035R70D010 2LBD1WMH

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.4
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)