

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P496302

Luminaire Tested: **LDA2B109035R70D010 2LBDL1H**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P496302
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-81)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B109035R70D010 2LBDL1H
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 3500K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 803.2 lumens
Efficiency: N/A
Efficacy: 80.3 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 10
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P496302
CATALOG NUMBER: LDA2B109035R70D010 2LBDL1H

Luminous Intensity Polar Plot





TEST NUMBER: P496302

CATALOG NUMBER: LDA2B109035R70D010 2LBDL1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	108	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85
3	101	94	89	84	99	93	88	84	90	86	82	87	84	81	85	82	80	78
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	74	71	67	66
6	85	75	68	64	83	74	68	63	72	67	63	71	66	63	70	65	62	61
7	80	70	63	59	78	69	63	58	68	62	58	66	61	58	65	61	57	56
8	75	65	59	54	74	64	58	54	63	58	54	62	57	53	61	57	53	52
9	71	61	54	50	70	60	54	50	59	54	50	58	53	50	57	53	49	48
10	68	57	51	47	66	57	50	46	56	50	46	55	50	46	54	49	46	45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	318021
5°	316165
10°	314060
15°	308196
20°	297059
25°	284430
30°	270942
35°	223568
40°	145295
45°	75912
50°	35307
55°	12902
60°	1283
65°	1051
70°	577
75°	762
80°	0
85°	0



TEST NUMBER: P496302

CATALOG NUMBER: LDA2B109035R70D010 2LBDL1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	60.4	7.5
10°-20°	169.6	21.1
20°-30°	240.7	30.0
30°-40°	225.1	28.0
40°-50°	90.5	11.3
50°-60°	15.8	2.0
60°-70°	0.8	0.1
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	470.6	58.6
0°-40°	695.7	86.6
0°-60°	802.0	99.9
0°-90°	803.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	803.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	645	
5°	638	60
15°	603	170
25°	522	241
35°	371	225
45°	109	91
55°	15	16
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P496302

CATALOG NUMBER: LDA2B109035R70D010 2LBDL1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	644.6
1°	645.4
2°	644.1
3°	641.5
4°	640.1
5°	638.4
6°	631.3
7°	633.5
8°	627.3
9°	626.0
10°	626.9
11°	621.1
12°	619.8
13°	612.7
14°	610.0
15°	603.4
16°	599.4
17°	591.5
18°	582.2
19°	576.9
20°	565.8
21°	557.4
22.5°	541.9
23°	537.9
24°	530.4
25°	522.5
26°	516.3
27°	507.4
28°	498.6
29°	487.9
30°	475.6
32.5°	432.2
35°	371.2
37.5°	299.1
40°	225.6
42.5°	161.0
45°	108.8
47.5°	71.7
50°	46.0
52.5°	28.8
55°	15.0
57.5°	4.9
60°	1.3
62.5°	0.9
65°	0.9



TEST NUMBER: P496302

CATALOG NUMBER: LDA2B109035R70D010 2LBDL1H

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.4
77.5°	0.4
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)