

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P279439

Luminaire Tested: **LDA2B108027D010 EU2B10FL408027 2LBALD1WH**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P279439  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-3)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA2B108027D010 EU2B10FL408027 2LBALD1WH  
Description: PORTFOLIO 2IN ADJ 1000 LUMEN LED LUMINAIRE WITH FLOOD OPTIC AND 2in  
ADJ spun Refl w/lens Self-Flanged, WH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1134.5 lumens  
Efficiency: N/A  
Efficacy: 113.4 lumens/watt  
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.55  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P279439

CATALOG NUMBER: LDA2B108027D010 EU2B10FL408027 2LBALD1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P279439

CATALOG NUMBER: LDA2B108027D010 EU2B10FL408027 2LBALD1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |    |    |    |    |    |    |    |    |    |   |     |  |  |  |  |  |    |  |  |  |  |  |  |  |  |    |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|----|----|----|----|----|----|----|----|---|-----|--|--|--|--|--|----|--|--|--|--|--|--|--|--|----|
| RF  | 20  |     |     |     |     |     |     |     |     | 20  |     |     |     |     |     |     |     |     | 20 |    |    |    |    |    |    |    |    | 20 |    |   |     |  |  |  |  |  | 20 |  |  |  |  |  |  |  |  | 20 |
| RC  | 80  |     |     |     |     |     |     |     |     | 70  |     |     |     |     |     |     |     |     | 50 |    |    |    |    |    |    |    |    | 30 |    |   |     |  |  |  |  |  | 10 |  |  |  |  |  |  |  |  | 0  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |     |  |  |  |  |  |    |  |  |  |  |  |  |  |  |    |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |    |    |    |    |    |    |    |    |    |   |     |  |  |  |  |  |    |  |  |  |  |  |  |  |  |    |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |    |    |    |    |    |    |    |    |    |   | 100 |  |  |  |  |  |    |  |  |  |  |  |  |  |  |    |
| 1   | 115 | 113 | 111 | 109 | 112 | 110 | 109 | 107 | 106 | 105 | 104 | 103 | 102 | 101 | 99  | 99  | 98  | 96  |    |    |    |    |    |    |    |    |    |    |    |   | 96  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |    |
| 2   | 111 | 107 | 104 | 101 | 109 | 105 | 102 | 100 | 102 | 100 | 98  | 99  | 97  | 96  | 97  | 95  | 94  | 92  |    |    |    |    |    |    |    |    |    |    |    |   | 92  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |    |
| 3   | 107 | 102 | 98  | 95  | 105 | 101 | 97  | 94  | 98  | 95  | 93  | 96  | 94  | 92  | 94  | 92  | 90  | 89  |    |    |    |    |    |    |    |    |    |    |    |   | 89  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |    |
| 4   | 103 | 98  | 93  | 90  | 102 | 97  | 93  | 90  | 95  | 91  | 89  | 93  | 90  | 88  | 91  | 89  | 87  | 85  |    |    |    |    |    |    |    |    |    |    |    |   | 85  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |    |
| 5   | 100 | 94  | 89  | 86  | 98  | 93  | 89  | 86  | 91  | 88  | 85  | 90  | 87  | 84  | 88  | 86  | 83  | 82  |    |    |    |    |    |    |    |    |    |    |    |   | 82  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |    |
| 6   | 97  | 90  | 85  | 82  | 95  | 89  | 85  | 82  | 88  | 84  | 82  | 87  | 83  | 81  | 85  | 83  | 80  | 79  |    |    |    |    |    |    |    |    |    |    |    |   | 79  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |    |
| 7   | 94  | 87  | 82  | 79  | 92  | 86  | 82  | 79  | 85  | 81  | 78  | 84  | 81  | 78  | 83  | 80  | 78  | 77  |    |    |    |    |    |    |    |    |    |    |    |   | 77  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |    |
| 8   | 91  | 84  | 79  | 76  | 90  | 83  | 79  | 76  | 82  | 78  | 76  | 81  | 78  | 75  | 80  | 77  | 75  | 74  |    |    |    |    |    |    |    |    |    |    |    |   | 74  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |    |
| 9   | 88  | 81  | 76  | 73  | 87  | 80  | 76  | 73  | 79  | 76  | 73  | 79  | 75  | 73  | 78  | 75  | 73  | 72  |    |    |    |    |    |    |    |    |    |    |    |   | 72  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |    |
| 10  | 85  | 78  | 74  | 71  | 84  | 78  | 74  | 71  | 77  | 73  | 71  | 76  | 73  | 70  | 76  | 72  | 70  | 69  |    |    |    |    |    |    |    |    |    |    |    |   | 69  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |    |

**AVERAGE LUMINANCE (cd/sqm):**

|     |         |
|-----|---------|
|     | 0°      |
| 0°  | 1559961 |
| 5°  | 1526993 |
| 10° | 1391752 |
| 15° | 1087216 |
| 20° | 643680  |
| 25° | 239303  |
| 30° | 74743   |
| 35° | 33246   |
| 40° | 15457   |
| 45° | 7256    |
| 50° | 3991    |
| 55° | 2236    |
| 60° | 987     |
| 65° | 584     |
| 70° | 721     |
| 75° | 0       |
| 80° | 0       |
| 85° | 0       |



TEST NUMBER: P279439

CATALOG NUMBER: LDA2B108027D010 EU2B10FL408027 2LBALD1WH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 285.0  | 25.1      |
| 10°-20°   | 566.8  | 50.0      |
| 20°-30°   | 232.1  | 20.5      |
| 30°-40°   | 38.4   | 3.4       |
| 40°-50°   | 9.1    | 0.8       |
| 50°-60°   | 2.4    | 0.2       |
| 60°-70°   | 0.6    | 0.0       |
| 70°-80°   | 0.1    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1083.9 | 95.5      |
| 0°-40°    | 1122.3 | 98.9      |
| 0°-60°    | 1133.8 | 99.9      |
| 0°-90°    | 1134.5 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1134.5 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 3162 |      |
| 5°  | 3083 | 285  |
| 15° | 2129 | 567  |
| 25° | 440  | 232  |
| 35° | 55   | 38   |
| 45° | 10   | 9    |
| 55° | 3    | 2    |
| 65° | 0    | 1    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P279439

CATALOG NUMBER: LDA2B108027D010 EU2B10FL408027 2LBALD1WH

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 3161.9 |
| 1°    | 3151.0 |
| 2°    | 3136.4 |
| 3°    | 3123.4 |
| 4°    | 3106.2 |
| 5°    | 3083.3 |
| 6°    | 3049.4 |
| 7°    | 3005.1 |
| 8°    | 2942.1 |
| 9°    | 2865.6 |
| 10°   | 2778.1 |
| 11°   | 2676.5 |
| 12°   | 2561.9 |
| 13°   | 2431.2 |
| 14°   | 2285.9 |
| 15°   | 2128.6 |
| 17.5° | 1688.0 |
| 20°   | 1226.0 |
| 22.5° | 784.9  |
| 25°   | 439.6  |
| 27.5° | 231.8  |
| 30°   | 131.2  |
| 32.5° | 83.3   |
| 35°   | 55.2   |
| 37.5° | 36.5   |
| 40°   | 24.0   |
| 42.5° | 15.6   |
| 45°   | 10.4   |
| 47.5° | 7.3    |
| 50°   | 5.2    |
| 52.5° | 3.6    |
| 55°   | 2.6    |
| 57.5° | 1.6    |
| 60°   | 1.0    |
| 62.5° | 0.5    |
| 65°   | 0.5    |
| 67.5° | 0.5    |
| 70°   | 0.5    |
| 72.5° | 0.0    |
| 75°   | 0.0    |
| 77.5° | 0.0    |
| 80°   | 0.0    |
| 82.5° | 0.0    |



TEST NUMBER: P279439

CATALOG NUMBER: LDA2B108027D010 EU2B10FL408027 2LBALD1WH

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







|       |  |     |
|-------|--|-----|
| 85°   |  | 0.0 |
| 87.5° |  | 0.0 |



(END OF REPORT)