

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P279546

Luminaire Tested: **LDA2B109030D010 EU2B10FL409030 2LBALD1LI**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P279546  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-3)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA2B109030D010 EU2B10FL409030 2LBALD1LI  
Description: PORTFOLIO 2IN ADJ 1000 LUMEN LED LUMINAIRE WITH FLOOD OPTIC AND 2in  
ADJ spun Refl w/lens Self-Flanged, H  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 933.6 lumens  
Efficiency: N/A  
Efficacy: 93.4 lumens/watt  
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.55  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P279546

CATALOG NUMBER: LDA2B109030D010 EU2B10FL409030 2LBALD1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P279546

CATALOG NUMBER: LDA2B109030D010 EU2B10FL409030 2LBALD1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96		
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92		
3	107	102	98	95	105	101	97	94	98	95	93	96	94	92	94	92	90	89		
4	103	98	93	90	102	97	93	90	95	91	89	93	90	88	91	89	87	85		
5	100	94	89	86	98	93	89	86	91	88	85	90	87	84	88	86	83	82		
6	97	90	85	82	95	89	85	82	88	84	82	87	83	81	85	83	80	79		
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77		
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74		
9	88	81	76	73	87	80	76	73	79	76	73	79	75	73	78	75	73	72		
10	85	78	74	71	84	78	74	71	77	73	71	76	73	70	76	72	70	69		

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1283777
5°	1256638
10°	1145324
15°	894708
20°	529750
25°	196897
30°	61526
35°	27344
40°	12688
45°	6000
50°	3300
55°	1806
60°	888
65°	467
70°	577
75°	0
80°	0
85°	0



TEST NUMBER: P279546

CATALOG NUMBER: LDA2B109030D010 EU2B10FL409030 2LBALD1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	234.5	25.1
10°-20°	466.4	50.0
20°-30°	191.0	20.5
30°-40°	31.6	3.4
40°-50°	7.5	0.8
50°-60°	2.0	0.2
60°-70°	0.5	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	892.0	95.5
0°-40°	923.6	98.9
0°-60°	933.1	99.9
0°-90°	933.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	933.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2602	
5°	2537	235
15°	1752	466
25°	362	191
35°	45	32
45°	9	7
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P279546

CATALOG NUMBER: LDA2B109030D010 EU2B10FL409030 2LBALD1LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2602.1
1°	2593.1
2°	2581.1
3°	2570.4
4°	2556.2
5°	2537.4
6°	2509.5
7°	2473.1
8°	2421.2
9°	2358.2
10°	2286.2
11°	2202.6
12°	2108.3
13°	2000.8
14°	1881.2
15°	1751.7
17.5°	1389.1
20°	1009.0
22.5°	645.9
25°	361.7
27.5°	190.7
30°	108.0
32.5°	68.6
35°	45.4
37.5°	30.0
40°	19.7
42.5°	12.9
45°	8.6
47.5°	6.0
50°	4.3
52.5°	3.0
55°	2.1
57.5°	1.3
60°	0.9
62.5°	0.4
65°	0.4
67.5°	0.4
70°	0.4
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P279546

CATALOG NUMBER: LDA2B109030D010 EU2B10FL409030 2LBALD1LI

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)