

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P278539

Luminaire Tested: **LDA2B108027D010 EU2B10NFL258027 2LBALD1H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P278539
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B108027D010 EU2B10NFL258027 2LBALD1H
Description: PORTFOLIO 2IN ADJ 1000 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC
AND 2in ADJ spun Refl w/lens Self-Flanged, LI
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1037.0 lumens
Efficiency: N/A
Efficacy: 103.7 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P278539

CATALOG NUMBER: LDA2B108027D010 EU2B10NFL258027 2LBALD1H

Luminous Intensity Polar Plot





TEST NUMBER: P278539

CATALOG NUMBER: LDA2B108027D010 EU2B10NFL258027 2LBALD1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	115	113	111	110	113	111	109	108	107	106	105	103	102	102	100	99	99	97				97															
2	112	108	105	103	110	107	104	102	103	101	100	101	99	98	98	97	96	94				94															
3	108	104	100	98	107	103	99	97	100	98	95	98	96	94	96	94	93	91				91															
4	105	100	96	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89				89															
5	102	97	93	90	101	96	92	90	94	91	89	93	90	88	92	89	87	86				86															
6	100	94	90	87	98	93	89	87	92	89	86	91	88	86	89	87	85	84				84															
7	97	91	87	84	96	90	87	84	89	86	84	88	85	83	87	85	83	82				82															
8	95	88	85	82	94	88	84	82	87	84	81	86	83	81	85	83	81	80				80															
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78				78															
10	90	84	80	78	90	84	80	78	83	80	77	82	79	77	82	79	77	76				76															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2654336
5°	2447953
10°	1649603
15°	813343
20°	347409
25°	136581
30°	53778
35°	23549
40°	11335
45°	5442
50°	2993
55°	1720
60°	987
65°	584
70°	721
75°	0
80°	0
85°	0



TEST NUMBER: P278539

CATALOG NUMBER: LDA2B108027D010 EU2B10NFL258027 2LBALD1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	418.7	40.4
10°-20°	450.9	43.5
20°-30°	130.2	12.6
30°-40°	27.5	2.6
40°-50°	6.8	0.7
50°-60°	2.0	0.2
60°-70°	0.7	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	999.8	96.4
0°-40°	1027.3	99.1
0°-60°	1036.0	99.9
0°-90°	1037.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1037.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5380	
5°	4943	419
15°	1592	451
25°	251	130
35°	39	27
45°	8	7
55°	2	2
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P278539

CATALOG NUMBER: LDA2B108027D010 EU2B10NFL258027 2LBALD1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	5380.1
1°	5346.3
2°	5289.1
3°	5211.8
4°	5102.3
5°	4942.9
6°	4727.7
7°	4447.0
8°	4101.7
9°	3699.2
10°	3292.8
11°	2882.0
12°	2494.2
13°	2149.9
14°	1847.2
15°	1592.4
17.5°	1052.4
20°	661.7
22.5°	406.9
25°	250.9
27.5°	153.1
30°	94.4
32.5°	59.7
35°	39.1
37.5°	25.9
40°	17.6
42.5°	12.2
45°	7.8
47.5°	4.9
50°	3.9
52.5°	2.9
55°	2.0
57.5°	1.5
60°	1.0
62.5°	1.0
65°	0.5
67.5°	0.5
70°	0.5
72.5°	0.5
75°	0.0
77.5°	0.5
80°	0.0
82.5°	0.0



TEST NUMBER: P278539

CATALOG NUMBER: LDA2B108027D010 EU2B10NFL258027 2LBALD1H

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)