

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P494392

Luminaire Tested: **LDA2B108027R20D010 2LBDC1MMS**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P494392  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/8/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B108027R20D010 2LBDC1MMS  
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 2700K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1062.9 lumens  
Efficiency: N/A  
Efficacy: 106.3 lumens/watt  
Spacing Criteria (0/90/45): 0.33 / 0.33 / 0.32  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P494392

CATALOG NUMBER: LDA2B108027R20D010 2LBDC1MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P494392

CATALOG NUMBER: LDA2B108027R20D010 2LBDC1MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20							
RC	80				70				50				30				10							
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10				
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	111	106	106	106	106	102	102	102	102	100	100	100	100
1	116	114	112	110	113	111	110	109	108	106	105	105	104	103	102	102	101	100	99	99	98	98	98	98
2	112	109	106	104	110	107	105	103	104	102	101	101	102	100	99	99	99	98	97	97	97	96	95	95
3	109	105	102	100	108	104	101	99	102	99	97	97	99	97	96	96	97	96	94	94	94	93	92	92
4	107	102	99	96	105	101	98	95	99	96	94	94	97	95	93	93	96	94	92	92	92	90	89	89
5	104	99	95	93	103	98	95	92	97	94	92	92	95	93	91	91	94	92	90	90	90	88	87	87
6	102	96	93	90	101	96	92	90	95	92	89	89	93	91	89	89	92	90	88	88	88	86	85	85
7	100	94	91	88	99	94	90	88	92	90	87	87	92	89	87	87	91	88	87	87	87	85	84	84
8	98	92	88	86	97	91	88	86	91	88	86	86	90	87	85	85	89	87	85	85	85	83	82	82
9	96	90	87	84	95	90	86	84	89	86	84	84	88	86	84	84	88	85	83	83	83	81	80	80
10	94	88	85	83	93	88	85	82	87	84	82	82	87	84	82	82	86	84	82	82	82	80	79	79

**AVERAGE LUMINANCE (cd/sqm):**

0°	
0°	3939642
5°	3282443
10°	1925038
15°	674262
20°	226968
25°	87479
30°	40163
35°	17767
40°	8695
45°	5093
50°	2763
55°	860
60°	493
65°	584
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P494392

CATALOG NUMBER: LDA2B108027R20D010 2LBDC1MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	542.3	51.0
10°-20°	407.2	38.3
20°-30°	85.6	8.0
30°-40°	20.5	1.9
40°-50°	5.9	0.6
50°-60°	1.2	0.1
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1035.0	97.4
0°-40°	1055.5	99.3
0°-60°	1062.6	100.0
0°-90°	1062.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1062.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	7985	
5°	6628	542
15°	1320	407
25°	161	86
35°	30	21
45°	7	6
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P494392

CATALOG NUMBER: LDA2B108027R20D010 2LBDC1MMS

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	7985.3
1°	7887.9
2°	7649.5
3°	7374.8
4°	7067.4
5°	6627.9
6°	6161.4
7°	5643.7
8°	5052.3
9°	4455.2
10°	3842.6
11°	3212.4
12°	2657.3
13°	2115.7
14°	1683.9
15°	1320.1
16°	1035.5
17°	816.8
18°	656.7
19°	532.3
20°	432.3
22.5°	262.3
25°	160.7
27.5°	105.2
30°	70.5
32.5°	43.0
35°	29.5
37.5°	20.2
40°	13.5
42.5°	9.8
45°	7.3
47.5°	5.2
50°	3.6
52.5°	2.1
55°	1.0
57.5°	0.5
60°	0.5
62.5°	0.5
65°	0.5
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0



TEST NUMBER: P494392

CATALOG NUMBER: LDA2B108027R20D010 2LBDC1MMS

**CANDELA DISTRIBUTION (continued):**

	0°
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)