

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P279550

Luminaire Tested: **LDA2B109030D010 EU2B10FL409030 2LBALD1WMH**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P279550  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-3)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA2B109030D010 EU2B10FL409030 2LBALD1WMH  
Description: PORTFOLIO 2IN ADJ 1000 LUMEN LED LUMINAIRE WITH FLOOD OPTIC AND 2in  
ADJ spun Refl w/lens Self-Flanged, WMH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 920.0 lumens  
Efficiency: N/A  
Efficacy: 92.0 lumens/watt  
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.55  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P279550

CATALOG NUMBER: LDA2B109030D010 EU2B10FL409030 2LBALD1WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P279550

CATALOG NUMBER: LDA2B109030D010 EU2B10FL409030 2LBALD1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92
3	107	102	98	95	105	101	97	94	98	95	93	96	94	92	94	92	90	89
4	103	98	93	90	102	97	93	90	95	91	89	93	90	88	91	89	87	85
5	100	94	89	86	98	93	89	86	91	88	85	90	87	84	88	86	84	82
6	97	90	85	82	95	89	85	82	88	84	82	87	83	81	85	83	80	79
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74
9	88	81	76	73	87	80	76	73	79	76	73	79	75	73	78	75	73	72
10	85	78	74	71	84	78	74	71	77	73	71	76	73	70	76	72	70	69

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1265128
5°	1238363
10°	1128691
15°	881735
20°	522032
25°	194066
30°	60614
35°	26982
40°	12494
45°	5861
50°	3224
55°	1806
60°	789
65°	467
70°	577
75°	0
80°	0
85°	0



TEST NUMBER: P279550

CATALOG NUMBER: LDA2B109030D010 EU2B10FL409030 2LBALD1WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	231.1	25.1
10°-20°	459.7	50.0
20°-30°	188.3	20.5
30°-40°	31.2	3.4
40°-50°	7.4	0.8
50°-60°	2.0	0.2
60°-70°	0.4	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	879.1	95.5
0°-40°	910.2	98.9
0°-60°	919.5	99.9
0°-90°	920.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	920.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2564	
5°	2500	231
15°	1726	460
25°	356	188
35°	45	31
45°	8	7
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P279550

CATALOG NUMBER: LDA2B109030D010 EU2B10FL409030 2LBALD1WMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2564.3
1°	2555.5
2°	2543.6
3°	2533.1
4°	2519.1
5°	2500.5
6°	2473.1
7°	2437.2
8°	2386.1
9°	2324.0
10°	2253.0
11°	2170.7
12°	2077.7
13°	1971.7
14°	1853.9
15°	1726.3
17.5°	1369.0
20°	994.3
22.5°	636.5
25°	356.5
27.5°	188.0
30°	106.4
32.5°	67.6
35°	44.8
37.5°	29.6
40°	19.4
42.5°	12.7
45°	8.4
47.5°	5.9
50°	4.2
52.5°	3.0
55°	2.1
57.5°	1.3
60°	0.8
62.5°	0.4
65°	0.4
67.5°	0.4
70°	0.4
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P279550

CATALOG NUMBER: LDA2B109030D010 EU2B10FL409030 2LBALD1WMH

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)