

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P278644

Luminaire Tested: **LDA2B109030D010 EU2B10NFL259030 2LBAD1MW**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P278644  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA2B109030D010 EU2B10NFL259030 2LBAD1MW  
Description: PORTFOLIO 2IN ADJ 1000 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC  
AND 2in ADJ spun Refl, Self-Flanged, MW  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 914.0 lumens  
Efficiency: N/A  
Efficacy: 91.4 lumens/watt  
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P278644

CATALOG NUMBER: LDA2B109030D010 EU2B10NFL259030 2LBAD1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P278644

CATALOG NUMBER: LDA2B109030D010 EU2B10NFL259030 2LBAD1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	113	111	110	113	111	109	108	107	106	105	103	102	102	100	99	99	97	97	97	97
2	112	108	105	103	110	107	104	102	103	101	100	101	99	98	98	97	96	94	94	94	94
3	108	104	100	98	107	103	99	97	100	98	95	98	96	94	96	94	93	91	91	91	91
4	105	100	96	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89	89	89	89
5	102	97	93	90	101	96	92	90	94	91	89	93	90	88	92	89	87	86	86	86	86
6	100	94	90	87	98	93	89	87	92	89	86	91	88	86	89	87	85	84	84	84	84
7	97	91	87	84	96	90	87	84	89	86	84	88	85	83	87	85	83	82	82	82	82
8	95	88	85	82	94	88	84	82	87	84	81	86	83	81	85	83	81	80	80	80	80
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78	78	78	78
10	90	84	80	78	90	84	80	78	83	80	78	82	79	77	82	79	77	76	76	76	76

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	2339620
5°	2157689
10°	1454023
15°	716911
20°	306194
25°	120359
30°	47398
35°	20779
40°	9983
45°	4814
50°	2610
55°	1462
60°	888
65°	467
70°	577
75°	0
80°	0
85°	0



TEST NUMBER: P278644

CATALOG NUMBER: LDA2B109030D010 EU2B10NFL259030 2LBAD1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	369.1	40.4
10°-20°	397.5	43.5
20°-30°	114.7	12.6
30°-40°	24.2	2.6
40°-50°	6.0	0.7
50°-60°	1.7	0.2
60°-70°	0.6	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	881.3	96.4
0°-40°	905.5	99.1
0°-60°	913.2	99.9
0°-90°	914.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	914.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4742	
5°	4357	369
15°	1404	397
25°	221	115
35°	34	24
45°	7	6
55°	2	2
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P278644

CATALOG NUMBER: LDA2B109030D010 EU2B10NFL259030 2LBAD1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4742.2
1°	4712.4
2°	4662.0
3°	4593.9
4°	4497.3
5°	4356.8
6°	4167.1
7°	3919.7
8°	3615.4
9°	3260.6
10°	2902.4
11°	2540.3
12°	2198.5
13°	1895.0
14°	1628.1
15°	1403.6
17.5°	927.7
20°	583.2
22.5°	358.6
25°	221.1
27.5°	134.9
30°	83.2
32.5°	52.6
35°	34.5
37.5°	22.8
40°	15.5
42.5°	10.8
45°	6.9
47.5°	4.3
50°	3.4
52.5°	2.6
55°	1.7
57.5°	1.3
60°	0.9
62.5°	0.9
65°	0.4
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.0
77.5°	0.4
80°	0.0
82.5°	0.0



TEST NUMBER: P278644

CATALOG NUMBER: LDA2B109030D010 EU2B10NFL259030 2LBAD1MW

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)