

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P494542

Luminaire Tested: **LDA2B108027R65D010 2LBD1LI**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P494542
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-66)
Test Lab: INNOVATION CENTER
Issue Date: 3/8/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B108027R65D010 2LBD1LI
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 2700K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1049.4 lumens
Efficiency: N/A
Efficacy: 104.9 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.95
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 10
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P494542
CATALOG NUMBER: LDA2B108027R65D010 2LBD1LI

Luminous Intensity Polar Plot





TEST NUMBER: P494542

CATALOG NUMBER: LDA2B108027R65D010 2LBD1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75
5	92	83	78	73	90	82	77	73	81	76	72	79	75	72	77	74	71	69
6	87	78	72	68	86	77	72	67	76	71	67	74	70	66	73	69	66	65
7	83	73	67	63	81	73	67	63	71	66	62	70	65	62	69	65	62	60
8	78	69	63	58	77	68	62	58	67	62	58	66	61	58	65	61	58	56
9	75	65	59	55	73	64	58	54	63	58	54	62	58	54	61	57	54	53
10	71	61	55	51	70	61	55	51	60	55	51	59	54	51	58	54	51	49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	570228
5°	524416
10°	501123
15°	481295
20°	443278
25°	410505
30°	376163
35°	276267
40°	130869
45°	43049
50°	13892
55°	1806
60°	987
65°	584
70°	721
75°	0
80°	0
85°	0



TEST NUMBER: P494542

CATALOG NUMBER: LDA2B108027R65D010 2LBD1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.5	9.5
10°-20°	262.1	25.0
20°-30°	347.6	33.1
30°-40°	275.0	26.2
40°-50°	60.1	5.7
50°-60°	4.5	0.4
60°-70°	0.6	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	709.1	67.6
0°-40°	984.1	93.8
0°-60°	1048.7	99.9
0°-90°	1049.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1049.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1156	
5°	1059	99
15°	942	262
25°	754	348
35°	459	275
45°	62	60
55°	2	4
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P494542

CATALOG NUMBER: LDA2B108027R65D010 2LBD1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1155.8
1°	1149.6
2°	1128.3
3°	1105.0
4°	1080.6
5°	1058.9
6°	1044.9
7°	1030.9
8°	1021.6
9°	1007.6
10°	1000.3
11°	988.9
12°	975.9
13°	964.5
14°	951.6
15°	942.3
16°	918.4
17°	906.5
18°	886.8
19°	868.7
20°	844.3
21°	824.6
22.5°	798.7
23°	791.4
24°	771.7
25°	754.1
26°	743.2
27°	725.1
28°	707.5
29°	686.2
30°	660.3
32.5°	570.1
35°	458.7
37.5°	327.0
40°	203.2
42.5°	114.5
45°	61.7
47.5°	33.2
50°	18.1
52.5°	7.8
55°	2.1
57.5°	1.0
60°	1.0
62.5°	0.5
65°	0.5



TEST NUMBER: P494542

CATALOG NUMBER: LDA2B108027R65D010 2LBD1LI

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.5
70°	0.5
72.5°	0.5
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)