

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P494561

Luminaire Tested: **LDA2B108027R65D010 2LBDLC1MW**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P494561  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-68)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B108027R65D010 2LBDLC1MW  
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 2700K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1049.5 lumens  
Efficiency: N/A  
Efficacy: 104.9 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.94  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P494561

CATALOG NUMBER: LDA2B108027R65D010 2LBDLC1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P494561

CATALOG NUMBER: LDA2B108027R65D010 2LBDLC1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	87
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80
4	97	89	83	79	95	88	83	79	86	81	78	84	80	77	82	78	76	74
5	92	83	77	73	90	82	76	72	80	75	72	79	74	71	77	73	70	69
6	87	78	72	67	85	77	71	67	75	70	66	74	69	66	73	69	65	64
7	82	73	67	62	81	72	66	62	71	66	62	70	65	61	68	64	61	60
8	78	68	62	58	77	68	62	58	67	61	58	66	61	57	65	60	57	56
9	74	64	58	54	73	64	58	54	63	57	54	62	57	54	61	57	53	52
10	71	61	55	51	70	60	54	51	59	54	50	59	54	50	58	53	50	49

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	549062
5°	526199
10°	501073
15°	476238
20°	443016
25°	408981
30°	354857
35°	254585
40°	138275
45°	59097
50°	25405
55°	9204
60°	1677
65°	1284
70°	865
75°	0
80°	0
85°	0



TEST NUMBER: P494561

CATALOG NUMBER: LDA2B108027R65D010 2LBDLC1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	99.5	9.5
10°-20°	261.2	24.9
20°-30°	341.5	32.5
30°-40°	259.8	24.8
40°-50°	75.1	7.2
50°-60°	11.3	1.1
60°-70°	1.0	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	702.1	66.9
0°-40°	961.9	91.7
0°-60°	1048.3	99.9
0°-90°	1049.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1049.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1113	
5°	1062	99
15°	932	261
25°	751	341
35°	423	260
45°	85	75
55°	11	11
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P494561

CATALOG NUMBER: LDA2B108027R65D010 2LBDLC1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1112.9
1°	1109.0
2°	1102.8
3°	1090.5
4°	1077.0
5°	1062.5
6°	1048.4
7°	1036.1
8°	1024.3
9°	1013.7
10°	1000.2
11°	988.4
12°	976.1
13°	963.8
14°	950.3
15°	932.4
16°	918.9
17°	902.7
18°	878.0
19°	865.1
20°	843.8
21°	824.7
22.5°	795.6
23°	784.4
24°	767.0
25°	751.3
26°	730.5
27°	707.6
28°	682.3
29°	655.4
30°	622.9
32.5°	533.7
35°	422.7
37.5°	311.7
40°	214.7
42.5°	136.2
45°	84.7
47.5°	52.7
50°	33.1
52.5°	19.6
55°	10.7
57.5°	3.9
60°	1.7
62.5°	1.1
65°	1.1



TEST NUMBER: P494561

CATALOG NUMBER: LDA2B108027R65D010 2LBDLC1MW

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.6
70°	0.6
72.5°	0.6
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)