

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P496476

Luminaire Tested: **LDA2B109040R60D010 2LBDL1MW**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P496476  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-55)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B109040R60D010 2LBDL1MW  
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 4000K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 822.5 lumens  
Efficiency: N/A  
Efficacy: 82.3 lumens/watt  
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.86  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P496476

CATALOG NUMBER: LDA2B109040R60D010 2LBDL1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P496476

CATALOG NUMBER: LDA2B109040R60D010 2LBDL1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	101		101	100	98		98	97	96	94
2	108	103	100	96	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	95	91	87	93	89	86		90	87	85		88	85	83	82
4	98	90	85	81	96	89	84	81	87	83	80		85	82	79		83	80	78	76
5	93	85	79	75	91	84	79	75	82	78	74		81	77	73		79	76	73	71
6	88	80	74	70	87	79	74	70	78	73	69		76	72	69		75	71	68	67
7	84	75	69	65	83	74	69	65	73	68	65		72	68	64		71	67	64	63
8	80	71	65	61	79	70	65	61	69	64	61		68	64	60		67	63	60	59
9	76	67	61	57	75	67	61	57	66	61	57		65	60	57		64	60	57	55
10	73	63	58	54	72	63	58	54	62	57	54		61	57	54		61	57	53	52

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	486800
5°	474099
10°	461045
15°	438186
20°	400384
25°	343821
30°	255846
35°	150210
40°	71553
45°	33421
50°	16656
55°	5849
60°	1381
65°	1051
70°	721
75°	953
80°	0
85°	0



TEST NUMBER: P496476

CATALOG NUMBER: LDA2B109040R60D010 2LBDL1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	90.1	11.0
10°-20°	238.7	29.0
20°-30°	283.5	34.5
30°-40°	160.0	19.4
40°-50°	41.6	5.1
50°-60°	7.6	0.9
60°-70°	0.8	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	612.3	74.4
0°-40°	772.2	93.9
0°-60°	821.4	99.9
0°-90°	822.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	822.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	987	
5°	957	90
15°	858	239
25°	632	283
35°	249	160
45°	48	42
55°	7	8
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P496476

CATALOG NUMBER: LDA2B109040R60D010 2LBDL1MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	986.7
1°	987.2
2°	980.4
3°	974.5
4°	963.2
5°	957.3
6°	946.9
7°	939.3
8°	932.0
9°	927.1
10°	920.3
11°	907.2
12°	895.0
13°	888.2
14°	872.4
15°	857.9
16°	841.2
17°	821.3
18°	802.4
19°	779.8
20°	762.6
21°	739.1
22.5°	700.3
23°	693.5
24°	660.5
25°	631.6
26°	599.5
27°	562.5
28°	525.9
29°	490.2
30°	449.1
32.5°	345.6
35°	249.4
37.5°	170.3
40°	111.1
42.5°	72.7
45°	47.9
47.5°	32.5
50°	21.7
52.5°	13.6
55°	6.8
57.5°	2.7
60°	1.4
62.5°	0.9
65°	0.9



TEST NUMBER: P496476

CATALOG NUMBER: LDA2B109040R60D010 2LBDL1MW

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.5
70°	0.5
72.5°	0.5
75°	0.5
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)