

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P494595

Luminaire Tested: **LDA2B108030R20D010 2LBD1MMS-30DEG TILT**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P494595
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-2)
Test Lab: INNOVATION CENTER
Issue Date: 3/8/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B108030R20D010 2LBD1MMS-30DEG TILT
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 3000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 689.1 lumens
Efficiency: N/A
Efficacy: 68.9 lumens/watt
Spacing Criteria (0/90/45): 2.56 / 0.56 / 1.2
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 10
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P494595

CATALOG NUMBER: LDA2B108030R20D010 2LBD1MMS-30DEG TILT

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270°



TEST NUMBER: P494595

CATALOG NUMBER: LDA2B108030R20D010 2LBD1MMS-30DEG TILT

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74
4	92	83	76	71	90	82	75	70	79	74	70	77	73	69	75	71	68	66
5	86	75	68	63	84	74	68	63	73	67	62	71	66	62	69	65	61	59
6	80	69	62	56	78	68	61	56	66	60	56	65	59	55	63	59	55	53
7	74	63	55	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48
8	69	57	50	45	68	57	50	45	56	49	45	54	49	44	53	48	44	43
9	64	53	45	40	63	52	45	40	51	45	40	50	44	40	49	44	40	38
10	60	48	41	36	59	48	41	36	47	41	36	46	40	36	45	40	36	34

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	10953	10953	10953
5°	20949	9657	7082
10°	49997	8466	4759
15°	291392	6742	1890
20°	1453636	4148	578
25°	2650620	1415	0
30°	3108886	0	0
35°	2721057	0	0
40°	2009399	0	0
45°	724302	0	0
50°	150821	0	0
55°	34492	430	0
60°	10953	493	0
65°	2452	1284	0
70°	0	1587	721
75°	0	2097	0
80°	0	3125	0
85°	0	6227	0



TEST NUMBER: P494595

CATALOG NUMBER: LDA2B108030R20D010 2LBD1MMS-30DEG TILT

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2.5	0.4
10°-20°	37.9	5.5
20°-30°	255.2	37.0
30°-40°	298.1	43.3
40°-50°	86.9	12.6
50°-60°	5.8	0.8
60°-70°	1.1	0.2
70°-80°	0.9	0.1
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	295.5	42.9
0°-40°	593.6	86.1
0°-60°	686.4	99.6
0°-90°	689.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	689.1	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	22	22	22	22	22	
5°	42	31	20	16	14	6
15°	570	64	13	7	4	298
25°	4869	100	3	0	0	2156
35°	4518	54	0	0	0	2776
45°	1038	11	0	0	0	957
55°	40	2	0	0	0	51
65°	2	1	1	1	0	3
75°	0	1	1	1	0	0
85°	0	1	1	1	0	0
90°	0	0	0	0	0	



TEST NUMBER: P494595

CATALOG NUMBER: LDA2B108030R20D010 2LBD1MMS-30DEG TILT

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	22.2	22.2	22.2	22.2	22.2	22.2	22.2	22.2	22.2
2.5°	28.5	28.5	25.4	22.7	20.6	19.5	19.0	18.0	17.4
5°	42.3	37.0	30.6	23.8	19.5	18.0	16.4	14.8	14.3
7.5°	61.8	53.9	37.0	24.3	18.5	15.8	14.3	12.7	11.6
10°	99.8	77.7	45.4	24.3	16.9	13.7	11.6	10.0	9.5
12.5°	184.4	118.9	54.4	23.8	15.3	11.6	9.0	7.9	6.3
15°	570.5	246.2	64.5	22.7	13.2	9.0	6.9	4.2	3.7
17.5°	1475.5	574.8	71.8	20.1	10.6	6.3	3.2	2.6	2.6
20°	2768.7	1042.3	82.4	17.4	7.9	4.2	2.1	1.6	1.1
21°	3158.6	1275.3	87.7	16.4	6.9	2.6	1.6	0.5	0.5
22°	3764.6	1529.4	91.9	15.3	5.8	1.6	1.1	0.5	0.0
23°	4196.2	1691.6	96.1	13.7	4.2	1.6	0.5	0.0	0.0
24°	4627.8	1898.1	98.8	12.7	3.7	1.1	0.5	0.0	0.0
25°	4869.2	2070.3	99.8	11.6	2.6	0.5	0.0	0.0	0.0
26°	5067.8	2185.5	100.4	10.6	1.6	0.0	0.0	0.0	0.0
27°	5237.9	2319.2	99.3	9.5	1.6	0.0	0.0	0.0	0.0
28°	5334.6	2341.4	97.7	8.5	0.5	0.0	0.0	0.0	0.0
29°	5376.3	2314.4	93.0	7.4	0.5	0.0	0.0	0.0	0.0
30°	5457.2	2289.1	88.2	6.9	0.0	0.0	0.0	0.0	0.0
31°	5382.7	2205.1	82.4	5.8	0.0	0.0	0.0	0.0	0.0
32°	5091.1	2134.3	75.5	4.8	0.0	0.0	0.0	0.0	0.0
33°	5003.9	1989.0	68.1	4.2	0.0	0.0	0.0	0.0	0.0
34°	4839.6	1772.9	61.8	3.7	0.0	0.0	0.0	0.0	0.0
35°	4517.9	1594.4	53.9	3.2	0.0	0.0	0.0	0.0	0.0
36°	4293.4	1390.4	47.0	2.6	0.0	0.0	0.0	0.0	0.0
37°	4058.3	1212.4	41.7	2.1	0.0	0.0	0.0	0.0	0.0
38°	3766.1	1025.4	35.4	1.6	0.0	0.0	0.0	0.0	0.0
39°	3425.9	847.4	30.1	1.6	0.0	0.0	0.0	0.0	0.0
40°	3120.0	683.1	25.9	1.1	0.0	0.0	0.0	0.0	0.0
42.5°	1925.6	389.9	15.3	1.1	0.0	0.0	0.0	0.0	0.0
45°	1038.1	236.7	11.1	0.5	0.0	0.0	0.0	0.0	0.0
47.5°	478.1	110.4	7.9	0.5	0.0	0.0	0.0	0.0	0.0
50°	196.5	49.1	5.8	0.0	0.0	0.0	0.0	0.0	0.0
52.5°	70.8	27.5	3.7	0.0	0.0	0.5	0.0	0.0	0.0
55°	40.1	15.8	2.1	0.5	0.5	0.5	0.5	0.0	0.0
57.5°	19.0	9.0	0.5	0.5	0.5	0.5	0.5	0.0	0.0
60°	11.1	4.8	0.5	0.5	0.5	1.1	0.5	0.0	0.0
62.5°	5.3	1.6	0.5	1.1	1.1	1.1	1.1	0.5	0.0
65°	2.1	0.5	1.1	1.1	1.1	1.6	1.1	0.5	0.0
67.5°	0.5	0.5	1.1	1.1	1.1	1.6	1.1	0.5	0.5
70°	0.0	0.5	1.1	1.1	1.1	1.6	1.1	0.5	0.5
72.5°	0.0	0.5	1.1	1.1	1.1	1.6	1.1	0.5	0.5
75°	0.0	0.5	1.1	1.1	1.1	1.1	1.1	0.5	0.0
77.5°	0.0	0.5	1.1	1.1	1.1	1.1	1.1	0.5	0.0
80°	0.0	0.5	1.1	1.1	1.1	1.1	1.1	0.5	0.0



TEST NUMBER: P494595

CATALOG NUMBER: LDA2B108030R20D010 2LBD1MMS-30DEG TILT

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
82.5°	0.0	0.5	1.1	1.1	1.1	1.1	1.1	0.5	0.0
85°	0.0	0.5	1.1	1.1	1.1	1.1	1.1	0.5	0.0
87.5°	0.0	0.5	1.1	1.1	1.1	1.1	0.5	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)