

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P494757

Luminaire Tested: **LDA2B108030R65D010 2LBD1H**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P494757
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-66)
Test Lab: INNOVATION CENTER
Issue Date: 3/8/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B108030R65D010 2LBD1H
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 3000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1069.7 lumens
Efficiency: N/A
Efficacy: 107.0 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.95
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 10
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P494757
CATALOG NUMBER: LDA2B108030R65D010 2LBD1H

Luminous Intensity Polar Plot





TEST NUMBER: P494757

CATALOG NUMBER: LDA2B108030R65D010 2LBD1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	111	108	106	111	109	106	104	104	103	101		101	99	98		97	96	95	93
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92	90	88	87
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87	84	82	80
4	97	89	84	79	95	88	83	79	86	82	78		84	80	77		82	79	76	75
5	92	83	78	73	90	82	77	73	81	76	72		79	75	72		77	74	71	69
6	87	78	72	68	86	77	72	67	76	71	67		74	70	66		73	69	66	65
7	83	73	67	63	81	73	67	63	71	66	62		70	65	62		69	65	62	60
8	78	69	63	58	77	68	62	58	67	62	58		66	61	58		65	61	58	56
9	75	65	59	55	73	64	58	54	63	58	54		62	58	54		61	57	54	53
10	71	61	55	51	70	61	55	51	60	55	51		59	54	51		58	54	51	49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	581230
5°	534519
10°	510792
15°	490539
20°	451836
25°	418453
30°	383398
35°	281568
40°	133380
45°	43887
50°	14199
55°	1806
60°	1085
65°	584
70°	721
75°	0
80°	0
85°	0



TEST NUMBER: P494757

CATALOG NUMBER: LDA2B108030R65D010 2LBD1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	101.4	9.5
10°-20°	267.1	25.0
20°-30°	354.3	33.1
30°-40°	280.3	26.2
40°-50°	61.3	5.7
50°-60°	4.5	0.4
60°-70°	0.6	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	722.8	67.6
0°-40°	1003.1	93.8
0°-60°	1068.9	99.9
0°-90°	1069.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1069.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1178	
5°	1079	101
15°	960	267
25°	769	354
35°	468	280
45°	63	61
55°	2	5
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P494757

CATALOG NUMBER: LDA2B108030R65D010 2LBD1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	1178.1
1°	1171.7
2°	1150.1
3°	1126.3
4°	1101.5
5°	1079.3
6°	1065.0
7°	1050.8
8°	1041.2
9°	1027.0
10°	1019.6
11°	1008.0
12°	994.8
13°	983.1
14°	969.9
15°	960.4
16°	936.1
17°	924.0
18°	903.9
19°	885.4
20°	860.6
21°	840.5
22.5°	814.1
23°	806.7
24°	786.6
25°	768.7
26°	757.6
27°	739.1
28°	721.1
29°	699.4
30°	673.0
32.5°	581.1
35°	467.5
37.5°	333.3
40°	207.1
42.5°	116.8
45°	62.9
47.5°	33.8
50°	18.5
52.5°	7.9
55°	2.1
57.5°	1.1
60°	1.1
62.5°	0.5
65°	0.5



TEST NUMBER: P494757

CATALOG NUMBER: LDA2B108030R65D010 2LBD1H

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.5
70°	0.5
72.5°	0.5
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)