

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P279566

Luminaire Tested: **LDA2B109035D010 EU2B10FL409035 2LBALD1WMH**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P279566  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-3)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA2B109035D010 EU2B10FL409035 2LBALD1WMH  
Description: PORTFOLIO 2IN ADJ 1000 LUMEN LED LUMINAIRE WITH FLOOD OPTIC AND 2in  
ADJ spun Refl w/lens Self-Flanged, WMH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 955.2 lumens  
Efficiency: N/A  
Efficacy: 95.5 lumens/watt  
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.55  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P279566

CATALOG NUMBER: LDA2B109035D010 EU2B10FL409035 2LBALD1WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P279566

CATALOG NUMBER: LDA2B109035D010 EU2B10FL409035 2LBALD1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96		
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92		
3	107	102	98	95	105	101	97	94	98	95	93	96	94	92	94	92	90	89		
4	103	98	93	90	102	97	93	90	95	91	89	93	90	88	91	89	87	85		
5	100	94	89	86	98	93	89	86	91	88	85	90	87	84	88	86	83	82		
6	97	90	85	82	95	89	85	82	88	84	82	87	83	81	85	83	80	79		
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77		
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74		
9	88	81	76	73	87	80	76	73	79	76	73	79	75	73	78	75	73	72		
10	85	78	74	71	84	78	74	71	77	73	71	76	73	70	76	72	70	69		

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1313428
5°	1285660
10°	1171775
15°	915394
20°	541983
25°	201469
30°	62950
35°	28006
40°	13010
45°	6140
50°	3377
55°	1892
60°	888
65°	467
70°	577
75°	0
80°	0
85°	0



TEST NUMBER: P279566

CATALOG NUMBER: LDA2B109035D010 EU2B10FL409035 2LBALD1WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	240.0	25.1
10°-20°	477.2	50.0
20°-30°	195.4	20.5
30°-40°	32.4	3.4
40°-50°	7.7	0.8
50°-60°	2.0	0.2
60°-70°	0.5	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	912.6	95.5
0°-40°	945.0	98.9
0°-60°	954.7	99.9
0°-90°	955.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	955.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2662	
5°	2596	240
15°	1792	477
25°	370	195
35°	46	32
45°	9	8
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P279566

CATALOG NUMBER: LDA2B109035D010 EU2B10FL409035 2LBALD1WMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2662.2
1°	2653.0
2°	2640.7
3°	2629.7
4°	2615.3
5°	2596.0
6°	2567.5
7°	2530.2
8°	2477.1
9°	2412.7
10°	2339.0
11°	2253.5
12°	2157.0
13°	2047.0
14°	1924.6
15°	1792.2
17.5°	1421.2
20°	1032.3
22.5°	660.8
25°	370.1
27.5°	195.1
30°	110.5
32.5°	70.2
35°	46.5
37.5°	30.7
40°	20.2
42.5°	13.2
45°	8.8
47.5°	6.1
50°	4.4
52.5°	3.1
55°	2.2
57.5°	1.3
60°	0.9
62.5°	0.4
65°	0.4
67.5°	0.4
70°	0.4
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P279566

CATALOG NUMBER: LDA2B109035D010 EU2B10FL409035 2LBALD1WMH

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)