

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P314966

Luminaire Tested: **LDA2B10NFL8030D010 PINW1MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P314966
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B10NFL8030D010 PINW1MB
Description: PORTFOLIO 2IN ADJ 1000 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC
AND 2in Adj PinHole, White oculus black finish
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 992.2 lumens
Efficiency: N/A
Efficacy: 99.2 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P314966

CATALOG NUMBER: LDA2B10NFL8030D010 PINW1MB

Luminous Intensity Polar Plot





TEST NUMBER: P314966

CATALOG NUMBER: LDA2B10NFL8030D010 PINW1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	113	111	110	113	111	109	108	107	106	105	103	102	102	100	99	99	97	97	97	97
2	112	108	105	103	110	107	104	102	103	101	100	101	99	98	98	97	96	94	94	94	94
3	108	104	100	98	107	103	99	97	100	98	95	98	96	94	96	94	93	91	91	91	91
4	105	100	96	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89	89	89	89
5	102	97	93	90	101	96	92	90	94	91	89	93	90	88	92	89	87	86	86	86	86
6	100	94	90	87	98	93	89	87	92	89	86	91	88	86	89	87	85	84	84	84	84
7	97	91	87	84	96	90	87	84	89	86	84	88	85	83	87	85	83	82	82	82	82
8	95	88	85	82	94	88	84	82	87	84	81	86	83	81	85	83	81	80	80	80	80
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78	78	78	78
10	90	84	80	78	90	84	80	78	83	80	77	82	79	77	82	79	77	76	76	76	76

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2539580
5°	2342119
10°	1578314
15°	778152
20°	332393
25°	130647
30°	51443
35°	22525
40°	10820
45°	5233
50°	2840
55°	1634
60°	888
65°	584
70°	721
75°	0
80°	0
85°	0



TEST NUMBER: P314966

CATALOG NUMBER: LDA2B10NFL8030D010 PINW1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	400.6	40.4
10°-20°	431.4	43.5
20°-30°	124.6	12.6
30°-40°	26.3	2.6
40°-50°	6.5	0.7
50°-60°	1.9	0.2
60°-70°	0.6	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	956.6	96.4
0°-40°	982.9	99.1
0°-60°	991.2	99.9
0°-90°	992.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	992.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5148	
5°	4729	401
15°	1524	431
25°	240	125
35°	37	26
45°	8	6
55°	2	2
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P314966

CATALOG NUMBER: LDA2B10NFL8030D010 PINW1MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	5147.5
1°	5115.3
2°	5060.5
3°	4986.6
4°	4881.8
5°	4729.2
6°	4523.3
7°	4254.8
8°	3924.4
9°	3539.3
10°	3150.5
11°	2757.4
12°	2386.4
13°	2057.0
14°	1767.3
15°	1523.5
17.5°	1007.0
20°	633.1
22.5°	389.3
25°	240.0
27.5°	146.5
30°	90.3
32.5°	57.1
35°	37.4
37.5°	24.8
40°	16.8
42.5°	11.7
45°	7.5
47.5°	4.7
50°	3.7
52.5°	2.8
55°	1.9
57.5°	1.4
60°	0.9
62.5°	0.9
65°	0.5
67.5°	0.5
70°	0.5
72.5°	0.5
75°	0.0
77.5°	0.5
80°	0.0
82.5°	0.0



TEST NUMBER: P314966

CATALOG NUMBER: LDA2B10NFL8030D010 PINW1MB

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)