

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P278577

Luminaire Tested: **LDA2B108035D010 EU2B10NFL258035 2LBALD1GPH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P278577
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B108035D010 EU2B10NFL258035 2LBALD1GPH
Description: PORTFOLIO 2IN ADJ 1000 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC AND 2in ADJ spun Refl w/lens Self-Flanged, GPH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1068.7 lumens
Efficiency: N/A
Efficacy: 106.9 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P278577

CATALOG NUMBER: LDA2B108035D010 EU2B10NFL258035 2LBALD1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P278577

CATALOG NUMBER: LDA2B108035D010 EU2B10NFL258035 2LBALD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	115	113	111	110	113	111	109	108	107	106	105	103	102	102	100	99	99	97				97															
2	112	108	105	103	110	107	104	102	103	101	100	101	99	98	98	97	96	94				94															
3	108	104	100	98	107	103	99	97	100	98	95	98	96	94	96	94	93	91				91															
4	105	100	96	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89				89															
5	102	97	93	90	101	96	92	90	94	91	89	93	90	88	92	89	87	86				86															
6	100	94	90	87	98	93	89	87	92	89	86	91	88	86	89	87	85	84				84															
7	97	91	87	84	96	90	87	84	89	86	84	88	85	83	87	85	83	82				82															
8	95	88	85	82	94	88	84	82	87	84	81	86	83	81	85	83	81	80				80															
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78				78															
10	90	84	80	78	90	84	80	78	83	80	78	82	79	77	82	79	77	76				76															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2735494
5°	2522834
10°	1700051
15°	838218
20°	358014
25°	140773
30°	55430
35°	24272
40°	11657
45°	5652
50°	3070
55°	1720
60°	987
65°	584
70°	721
75°	0
80°	0
85°	0



TEST NUMBER: P278577

CATALOG NUMBER: LDA2B108035D010 EU2B10NFL258035 2LBALD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	431.5	40.4
10°-20°	464.7	43.5
20°-30°	134.2	12.6
30°-40°	28.3	2.6
40°-50°	7.0	0.7
50°-60°	2.0	0.2
60°-70°	0.7	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1030.4	96.4
0°-40°	1058.7	99.1
0°-60°	1067.7	99.9
0°-90°	1068.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1068.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5545	
5°	5094	432
15°	1641	465
25°	259	134
35°	40	28
45°	8	7
55°	2	2
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P278577

CATALOG NUMBER: LDA2B108035D010 EU2B10NFL258035 2LBALD1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	5544.6
1°	5509.9
2°	5450.9
3°	5371.3
4°	5258.4
5°	5094.1
6°	4872.3
7°	4583.0
8°	4227.2
9°	3812.4
10°	3393.5
11°	2970.1
12°	2570.5
13°	2215.6
14°	1903.7
15°	1641.1
17.5°	1084.6
20°	681.9
22.5°	419.3
25°	258.6
27.5°	157.8
30°	97.3
32.5°	61.5
35°	40.3
37.5°	26.7
40°	18.1
42.5°	12.6
45°	8.1
47.5°	5.0
50°	4.0
52.5°	3.0
55°	2.0
57.5°	1.5
60°	1.0
62.5°	1.0
65°	0.5
67.5°	0.5
70°	0.5
72.5°	0.5
75°	0.0
77.5°	0.5
80°	0.0
82.5°	0.0



TEST NUMBER: P278577

CATALOG NUMBER: LDA2B108035D010 EU2B10NFL258035 2LBALD1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)