

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P494832

Luminaire Tested: **LDA2B108035R20D010 2LBDL1MMS-30DEG TILT**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P494832
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-2)
Test Lab: INNOVATION CENTER
Issue Date: 3/8/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B108035R20D010 2LBDL1MMS-30DEG TILT
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 3500K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 596.5 lumens
Efficiency: N/A
Efficacy: 59.7 lumens/watt
Spacing Criteria (0/90/45): 2.56 / 0.56 / 1.2
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 10
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P494832

CATALOG NUMBER: LDA2B108035R20D010 2LBDL1MMS-30DEG TILT

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270°



TEST NUMBER: P494832

CATALOG NUMBER: LDA2B108035R20D010 2LBDL1MMS-30DEG TILT

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91					91			
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82					82			
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74					74			
4	92	83	76	71	90	82	75	70	79	74	70	77	73	69	75	71	68	66					66			
5	86	75	68	63	84	74	68	63	73	67	62	71	66	62	69	65	61	59					59			
6	80	69	62	56	78	68	61	56	66	60	56	65	59	55	63	59	55	53					53			
7	74	63	55	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48					48			
8	69	57	50	45	68	57	50	45	56	49	45	54	49	44	53	48	44	43					43			
9	64	53	45	40	63	52	45	40	51	45	40	50	44	40	49	44	40	38					38			
10	60	48	41	36	59	48	41	36	47	41	36	46	40	36	45	40	36	34					34			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	9473	9473	9473
5°	18126	8370	6092
10°	43284	7314	4108
15°	252267	5823	1634
20°	1258327	3623	473
25°	2294496	1252	0
30°	2691193	0	0
35°	2355471	0	0
40°	1739418	0	0
45°	626970	0	0
50°	130558	0	0
55°	29933	430	0
60°	9473	493	0
65°	2101	1051	0
70°	0	1298	721
75°	0	1716	0
80°	0	2557	0
85°	0	5095	0



TEST NUMBER: P494832

CATALOG NUMBER: LDA2B108035R20D010 2LBDL1MMS-30DEG TILT

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2.2	0.4
10°-20°	32.8	5.5
20°-30°	220.9	37.0
30°-40°	258.1	43.3
40°-50°	75.3	12.6
50°-60°	5.0	0.8
60°-70°	0.9	0.2
70°-80°	0.8	0.1
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	255.8	42.9
0°-40°	513.9	86.1
0°-60°	594.2	99.6
0°-90°	596.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	596.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	19	19	19	19	19	
5°	37	26	17	14	12	5
15°	494	56	11	6	3	258
25°	4215	86	2	0	0	1866
35°	3911	47	0	0	0	2403
45°	899	10	0	0	0	828
55°	35	2	0	0	0	44
65°	2	1	1	1	0	3
75°	0	1	1	1	0	0
85°	0	1	1	1	0	0
90°	0	0	0	0	0	



TEST NUMBER: P494832

CATALOG NUMBER: LDA2B108035R20D010 2LBDL1MMS-30DEG TILT

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	19.2	19.2	19.2	19.2	19.2	19.2	19.2	19.2	19.2
2.5°	24.7	24.7	22.0	19.7	17.8	16.9	16.5	15.5	15.1
5°	36.6	32.0	26.5	20.6	16.9	15.5	14.2	12.8	12.3
7.5°	53.5	46.6	32.0	21.0	16.0	13.7	12.3	11.0	10.1
10°	86.4	67.2	39.3	21.0	14.6	11.9	10.1	8.7	8.2
12.5°	159.6	102.9	47.1	20.6	13.3	10.1	7.8	6.9	5.5
15°	493.9	213.1	55.8	19.7	11.4	7.8	5.9	3.7	3.2
17.5°	1277.3	497.5	62.2	17.4	9.1	5.5	2.7	2.3	2.3
20°	2396.7	902.3	71.3	15.1	6.9	3.7	1.8	1.4	0.9
21°	2734.2	1103.9	75.9	14.2	5.9	2.3	1.4	0.5	0.5
22°	3258.8	1323.9	79.6	13.3	5.0	1.4	0.9	0.5	0.0
23°	3632.4	1464.3	83.2	11.9	3.7	1.4	0.5	0.0	0.0
24°	4006.0	1643.1	85.5	11.0	3.2	0.9	0.5	0.0	0.0
25°	4215.0	1792.2	86.4	10.1	2.3	0.5	0.0	0.0	0.0
26°	4386.9	1891.9	86.9	9.1	1.4	0.0	0.0	0.0	0.0
27°	4534.2	2007.6	86.0	8.2	1.4	0.0	0.0	0.0	0.0
28°	4617.9	2026.8	84.6	7.3	0.5	0.0	0.0	0.0	0.0
29°	4654.0	2003.5	80.5	6.4	0.5	0.0	0.0	0.0	0.0
30°	4724.0	1981.5	76.4	5.9	0.0	0.0	0.0	0.0	0.0
31°	4659.5	1908.8	71.3	5.0	0.0	0.0	0.0	0.0	0.0
32°	4407.0	1847.5	65.4	4.1	0.0	0.0	0.0	0.0	0.0
33°	4331.6	1721.8	59.0	3.7	0.0	0.0	0.0	0.0	0.0
34°	4189.4	1534.7	53.5	3.2	0.0	0.0	0.0	0.0	0.0
35°	3910.9	1380.1	46.6	2.7	0.0	0.0	0.0	0.0	0.0
36°	3716.5	1203.6	40.7	2.3	0.0	0.0	0.0	0.0	0.0
37°	3513.0	1049.5	36.1	1.8	0.0	0.0	0.0	0.0	0.0
38°	3260.1	887.6	30.6	1.4	0.0	0.0	0.0	0.0	0.0
39°	2965.6	733.5	26.1	1.4	0.0	0.0	0.0	0.0	0.0
40°	2700.8	591.3	22.4	0.9	0.0	0.0	0.0	0.0	0.0
42.5°	1666.9	337.5	13.3	0.9	0.0	0.0	0.0	0.0	0.0
45°	898.6	204.9	9.6	0.5	0.0	0.0	0.0	0.0	0.0
47.5°	413.9	95.6	6.9	0.5	0.0	0.0	0.0	0.0	0.0
50°	170.1	42.5	5.0	0.0	0.0	0.0	0.0	0.0	0.0
52.5°	61.3	23.8	3.2	0.0	0.0	0.5	0.0	0.0	0.0
55°	34.8	13.7	1.8	0.5	0.5	0.5	0.5	0.0	0.0
57.5°	16.5	7.8	0.5	0.5	0.5	0.5	0.5	0.0	0.0
60°	9.6	4.1	0.5	0.5	0.5	0.9	0.5	0.0	0.0
62.5°	4.6	1.4	0.5	0.9	0.9	0.9	0.9	0.5	0.0
65°	1.8	0.5	0.9	0.9	0.9	1.4	0.9	0.5	0.0
67.5°	0.5	0.5	0.9	0.9	0.9	1.4	0.9	0.5	0.5
70°	0.0	0.5	0.9	0.9	0.9	1.4	0.9	0.5	0.5
72.5°	0.0	0.5	0.9	0.9	0.9	1.4	0.9	0.5	0.5
75°	0.0	0.5	0.9	0.9	0.9	0.9	0.9	0.5	0.0
77.5°	0.0	0.5	0.9	0.9	0.9	0.9	0.9	0.5	0.0
80°	0.0	0.5	0.9	0.9	0.9	0.9	0.9	0.5	0.0



TEST NUMBER: P494832

CATALOG NUMBER: LDA2B108035R20D010 2LBDL1MMS-30DEG TILT

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
82.5°	0.0	0.5	0.9	0.9	0.9	0.9	0.9	0.5	0.0
85°	0.0	0.5	0.9	0.9	0.9	0.9	0.9	0.5	0.0
87.5°	0.0	0.5	0.9	0.9	0.9	0.9	0.5	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)