

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P494838

Luminaire Tested: **LDA2B108035R20D010 2LBDLC1MB-30DEG TILT**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P494838  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-2)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/8/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B108035R20D010 2LBDLC1MB-30DEG TILT  
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 3500K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 696.7 lumens  
Efficiency: N/A  
Efficacy: 69.7 lumens/watt  
Spacing Criteria (0/90/45): 2.56 / 0.56 / 1.2  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P494838

CATALOG NUMBER: LDA2B108035R20D010 2LBDLC1MB-30DEG TILT

### Luminous Intensity Polar Plot



— 0°-180°    - - 45°-225°    - - - 90°-270°



TEST NUMBER: P494838

CATALOG NUMBER: LDA2B108035R20D010 2LBDLC1MB-30DEG TILT

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74
4	92	83	76	71	90	82	75	70	79	74	70	77	73	69	75	71	68	66
5	86	75	68	63	84	74	68	63	73	67	62	71	66	62	69	65	61	59
6	80	69	62	56	78	68	61	56	66	60	56	65	59	55	63	59	55	53
7	74	63	55	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48
8	69	57	50	45	68	57	50	45	56	49	45	54	49	44	53	48	44	43
9	64	53	45	40	63	52	45	40	51	45	40	50	44	40	49	44	40	38
10	60	48	41	36	59	48	41	36	47	41	36	46	40	36	45	40	36	34

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	11051	11051	11051
5°	21147	9806	7132
10°	50598	8567	4809
15°	294661	6844	1890
20°	1469807	4200	578
25°	2680015	1470	0
30°	3143352	0	0
35°	2751231	0	0
40°	2031747	0	0
45°	732326	0	0
50°	152509	0	0
55°	34922	430	0
60°	11051	493	0
65°	2452	1284	0
70°	0	1587	721
75°	0	2097	0
80°	0	3125	0
85°	0	6227	0



TEST NUMBER: P494838

CATALOG NUMBER: LDA2B108035R20D010 2LBDLC1MB-30DEG TILT

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	2.5	0.4
10°-20°	38.3	5.5
20°-30°	258.0	37.0
30°-40°	301.4	43.3
40°-50°	87.9	12.6
50°-60°	5.9	0.8
60°-70°	1.1	0.2
70°-80°	0.9	0.1
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	298.8	42.9
0°-40°	600.2	86.2
0°-60°	694.0	99.6
0°-90°	696.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	696.7	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	22	22	22	22	22	
5°	43	31	20	17	14	6
15°	577	65	13	7	4	301
25°	4923	101	3	0	0	2180
35°	4568	54	0	0	0	2806
45°	1050	11	0	0	0	967
55°	41	2	0	0	0	52
65°	2	1	1	1	0	3
75°	0	1	1	1	0	0
85°	0	1	1	1	0	0
90°	0	0	0	0	0	



TEST NUMBER: P494838

CATALOG NUMBER: LDA2B108035R20D010 2LBDLC1MB-30DEG TILT

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	22.4	22.4	22.4	22.4	22.4	22.4	22.4	22.4	22.4
2.5°	28.8	28.8	25.6	23.0	20.8	19.8	19.2	18.2	17.6
5°	42.7	37.4	31.0	24.0	19.8	18.2	16.6	15.0	14.4
7.5°	62.5	54.5	37.4	24.6	18.7	16.0	14.4	12.8	11.8
10°	101.0	78.5	45.9	24.6	17.1	13.9	11.8	10.1	9.6
12.5°	186.4	120.2	55.0	24.0	15.5	11.8	9.1	8.0	6.4
15°	576.9	248.9	65.2	23.0	13.4	9.1	6.9	4.3	3.7
17.5°	1491.9	581.2	72.6	20.3	10.7	6.4	3.2	2.7	2.7
20°	2799.5	1053.9	83.3	17.6	8.0	4.3	2.1	1.6	1.1
21°	3193.7	1289.4	88.7	16.6	6.9	2.7	1.6	0.5	0.5
22°	3806.3	1546.4	92.9	15.5	5.9	1.6	1.1	0.5	0.0
23°	4242.7	1710.3	97.2	13.9	4.3	1.6	0.5	0.0	0.0
24°	4679.1	1919.2	99.9	12.8	3.7	1.1	0.5	0.0	0.0
25°	4923.2	2093.3	101.0	11.8	2.7	0.5	0.0	0.0	0.0
26°	5124.1	2209.8	101.5	10.7	1.6	0.0	0.0	0.0	0.0
27°	5296.1	2344.9	100.4	9.6	1.6	0.0	0.0	0.0	0.0
28°	5393.8	2367.3	98.8	8.5	0.5	0.0	0.0	0.0	0.0
29°	5436.0	2340.1	94.0	7.5	0.5	0.0	0.0	0.0	0.0
30°	5517.7	2314.5	89.2	6.9	0.0	0.0	0.0	0.0	0.0
31°	5442.4	2229.5	83.3	5.9	0.0	0.0	0.0	0.0	0.0
32°	5147.6	2157.9	76.4	4.8	0.0	0.0	0.0	0.0	0.0
33°	5059.4	2011.1	68.9	4.3	0.0	0.0	0.0	0.0	0.0
34°	4893.3	1792.6	62.5	3.7	0.0	0.0	0.0	0.0	0.0
35°	4568.0	1612.1	54.5	3.2	0.0	0.0	0.0	0.0	0.0
36°	4341.0	1405.9	47.5	2.7	0.0	0.0	0.0	0.0	0.0
37°	4103.3	1225.9	42.2	2.1	0.0	0.0	0.0	0.0	0.0
38°	3807.9	1036.8	35.8	1.6	0.0	0.0	0.0	0.0	0.0
39°	3463.9	856.8	30.4	1.6	0.0	0.0	0.0	0.0	0.0
40°	3154.7	690.7	26.2	1.1	0.0	0.0	0.0	0.0	0.0
42.5°	1947.0	394.2	15.5	1.1	0.0	0.0	0.0	0.0	0.0
45°	1049.6	239.3	11.2	0.5	0.0	0.0	0.0	0.0	0.0
47.5°	483.4	111.6	8.0	0.5	0.0	0.0	0.0	0.0	0.0
50°	198.7	49.7	5.9	0.0	0.0	0.0	0.0	0.0	0.0
52.5°	71.6	27.8	3.7	0.0	0.0	0.5	0.0	0.0	0.0
55°	40.6	16.0	2.1	0.5	0.5	0.5	0.5	0.0	0.0
57.5°	19.2	9.1	0.5	0.5	0.5	0.5	0.5	0.0	0.0
60°	11.2	4.8	0.5	0.5	0.5	1.1	0.5	0.0	0.0
62.5°	5.3	1.6	0.5	1.1	1.1	1.1	1.1	0.5	0.0
65°	2.1	0.5	1.1	1.1	1.1	1.6	1.1	0.5	0.0
67.5°	0.5	0.5	1.1	1.1	1.1	1.6	1.1	0.5	0.5
70°	0.0	0.5	1.1	1.1	1.1	1.6	1.1	0.5	0.5
72.5°	0.0	0.5	1.1	1.1	1.1	1.6	1.1	0.5	0.5
75°	0.0	0.5	1.1	1.1	1.1	1.1	1.1	0.5	0.0
77.5°	0.0	0.5	1.1	1.1	1.1	1.1	1.1	0.5	0.0
80°	0.0	0.5	1.1	1.1	1.1	1.1	1.1	0.5	0.0



TEST NUMBER: P494838

CATALOG NUMBER: LDA2B108035R20D010 2LBDLC1MB-30DEG TILT

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
82.5°	0.0	0.5	1.1	1.1	1.1	1.1	1.1	0.5	0.0
85°	0.0	0.5	1.1	1.1	1.1	1.1	1.1	0.5	0.0
87.5°	0.0	0.5	1.1	1.1	1.1	1.1	0.5	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)