

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P496705

Luminaire Tested: **LDA2B109050R65D010 2LBD1MW**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P496705  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-66)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/8/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B109050R65D010 2LBD1MW  
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 5000K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 939.9 lumens  
Efficiency: N/A  
Efficacy: 94.0 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.95  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P496705  
CATALOG NUMBER: LDA2B109050R65D010 2LBD1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P496705

CATALOG NUMBER: LDA2B109050R65D010 2LBD1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	111	108	106	111	109	106	104	104	103	101		101	99	98		97	96	95	93
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92	90	88	87
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87	84	82	80
4	97	89	84	79	95	88	83	79	86	82	78		84	80	77		82	79	76	75
5	92	83	78	73	90	82	77	73	81	76	72		79	75	72		77	74	71	69
6	87	78	72	68	86	77	72	67	76	71	67		74	70	66		73	69	66	65
7	83	73	67	63	81	73	67	63	71	66	62		70	65	62		69	65	62	60
8	78	69	63	58	77	68	62	58	67	62	58		66	61	58		65	61	58	56
9	75	65	59	55	73	64	58	54	63	58	54		62	58	54		61	57	54	53
10	71	61	55	51	70	61	55	51	60	55	51		59	54	51		58	54	51	49

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	510629
5°	469642
10°	448771
15°	430984
20°	396971
25°	367609
30°	336855
35°	247418
40°	117151
45°	38514
50°	12434
55°	1634
60°	888
65°	584
70°	721
75°	0
80°	0
85°	0



TEST NUMBER: P496705

CATALOG NUMBER: LDA2B109050R65D010 2LBD1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	89.1	9.5
10°-20°	234.7	25.0
20°-30°	311.3	33.1
30°-40°	246.3	26.2
40°-50°	53.8	5.7
50°-60°	4.0	0.4
60°-70°	0.5	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	635.1	67.6
0°-40°	881.3	93.8
0°-60°	939.1	99.9
0°-90°	939.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	939.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1035	
5°	948	89
15°	844	235
25°	675	311
35°	411	246
45°	55	54
55°	2	4
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P496705

CATALOG NUMBER: LDA2B109050R65D010 2LBD1MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1035.0
1°	1029.5
2°	1010.4
3°	989.6
4°	967.7
5°	948.3
6°	935.7
7°	923.2
8°	914.8
9°	902.3
10°	895.8
11°	885.6
12°	874.0
13°	863.8
14°	852.2
15°	843.8
16°	822.5
17°	811.8
18°	794.2
19°	777.9
20°	756.1
21°	738.5
22.5°	715.2
23°	708.8
24°	691.1
25°	675.3
26°	665.6
27°	649.3
28°	633.6
29°	614.5
30°	591.3
32.5°	510.6
35°	410.8
37.5°	292.9
40°	181.9
42.5°	102.6
45°	55.2
47.5°	29.7
50°	16.2
52.5°	7.0
55°	1.9
57.5°	0.9
60°	0.9
62.5°	0.5
65°	0.5



TEST NUMBER: P496705

CATALOG NUMBER: LDA2B109050R65D010 2LBD1MW

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.5
70°	0.5
72.5°	0.5
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)