

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P494861

Luminaire Tested: **LDA2B108035R30D010 2LBDC1MB**

Issue Date: 3/12/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P494861  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-14)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/12/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B108035R30D010 2LBDC1MB  
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 3500K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1019.4 lumens  
Efficiency: N/A  
Efficacy: 101.9 lumens/watt  
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.46  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P494861  
CATALOG NUMBER: LDA2B108035R30D010 2LBDC1MB

### Luminous Intensity Polar Plot





TEST NUMBER: P494861

CATALOG NUMBER: LDA2B108035R30D010 2LBDC1MB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20													
RC	80					70					50					30					10					0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0				
RCR																																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100	100	100	100	100	100	100	100	100	100		
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	97	96	95	94	93	92	91	90	89	88	87	86	85	84		
2	111	108	105	102	109	106	103	101	103	101	99	100	98	97	97	96	95	94	93	92	91	90	89	88	87	86	85	84	83	82	81	80		
3	108	103	100	97	106	102	99	96	99	97	94	97	95	93	95	93	92	91	90	89	88	87	86	85	84	83	82	81	80	79	78	77		
4	104	99	95	92	103	98	94	92	96	93	91	94	92	90	92	90	89	88	87	86	85	84	83	82	81	80	79	78	77	76	75	74		
5	101	95	91	88	100	95	91	88	93	90	87	91	89	86	90	88	86	85	84	83	82	81	80	79	78	77	76	75	74	73	72	71		
6	98	92	88	85	97	91	88	85	90	87	84	89	86	84	88	85	83	82	81	80	79	78	77	76	75	74	73	72	71	70	69	68		
7	96	89	85	82	95	89	85	82	87	84	81	86	83	81	85	83	81	80	79	78	77	76	75	74	73	72	71	70	69	68	67	66		
8	93	86	82	79	92	86	82	79	85	81	79	84	81	79	83	81	78	77	76	75	74	73	72	71	70	69	68	67	66	65	64	63	62	
9	90	84	80	77	90	83	80	77	83	79	77	82	79	76	81	78	76	75	74	73	72	71	70	69	68	67	66	65	64	63	62	61	60	
10	88	81	77	75	87	81	77	75	80	77	75	80	77	74	79	76	74	73	72	71	70	69	68	67	66	65	64	63	62	61	60	59	58	

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1975667
5°	1883769
10°	1527666
15°	933884
20°	408049
25°	152640
30°	63292
35°	29572
40°	13782
45°	6698
50°	3684
55°	1376
60°	493
65°	584
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P494861

CATALOG NUMBER: LDA2B108035R30D010 2LBDC1MB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	339.3	33.3
10°-20°	489.9	48.1
20°-30°	146.2	14.3
30°-40°	33.6	3.3
40°-50°	8.3	0.8
50°-60°	1.9	0.2
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	975.4	95.7
0°-40°	1009.0	99.0
0°-60°	1019.1	100.0
0°-90°	1019.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1019.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4004	
5°	3804	339
15°	1828	490
25°	280	146
35°	49	34
45°	10	8
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P494861

CATALOG NUMBER: LDA2B108035R30D010 2LBDC1MB

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	4004.5
1°	3995.4
2°	3954.8
3°	3927.6
4°	3876.8
5°	3803.7
6°	3703.8
7°	3584.7
8°	3433.0
9°	3248.1
10°	3049.4
11°	2836.8
12°	2595.4
13°	2335.8
14°	2089.0
15°	1828.4
16°	1576.3
17°	1327.9
18°	1127.6
19°	933.2
20°	777.2
21°	629.8
22.5°	466.8
23°	420.9
24°	344.5
25°	280.4
26°	230.2
27°	191.8
28°	158.1
29°	132.5
30°	111.1
32.5°	72.6
35°	49.1
37.5°	32.6
40°	21.4
42.5°	13.9
45°	9.6
47.5°	6.9
50°	4.8
52.5°	3.2
55°	1.6
57.5°	1.1
60°	0.5
62.5°	0.5
65°	0.5



TEST NUMBER: P494861

CATALOG NUMBER: LDA2B108035R30D010 2LBDC1MB

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)