

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P494951

Luminaire Tested: **LDA2B108035R60D010 2LBD1LI**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P494951
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-53)
Test Lab: INNOVATION CENTER
Issue Date: 3/8/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B108035R60D010 2LBD1LI
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 3500K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1054.1 lumens
Efficiency: N/A
Efficacy: 105.4 lumens/watt
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.87
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 10
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P494951
CATALOG NUMBER: LDA2B108035R60D010 2LBD1LI

Luminous Intensity Polar Plot





TEST NUMBER: P494951

CATALOG NUMBER: LDA2B108035R60D010 2LBD1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	108	104	100	96	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	96	91	88	93	89	86		91	87	85		88	86	84	82
4	98	91	86	81	96	90	85	81	88	83	80		86	82	79		84	81	78	77
5	93	85	80	75	92	84	79	75	83	78	74		81	77	74		79	76	73	72
6	89	80	74	70	87	79	74	70	78	73	70		77	72	69		75	72	69	67
7	85	76	70	66	83	75	69	66	74	69	65		73	68	65		71	67	64	63
8	81	71	66	62	79	71	65	61	70	65	61		69	64	61		68	64	61	59
9	77	68	62	58	76	67	62	58	66	61	58		65	61	57		64	60	57	56
10	73	64	58	55	72	64	58	54	63	58	54		62	57	54		61	57	54	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	631158
5°	599149
10°	586539
15°	567767
20°	519092
25°	460859
30°	344773
35°	194658
40°	73292
45°	32793
50°	15965
55°	3183
60°	1085
65°	584
70°	721
75°	0
80°	0
85°	0



TEST NUMBER: P494951

CATALOG NUMBER: LDA2B108035R60D010 2LBD1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	114.5	10.9
10°-20°	308.7	29.3
20°-30°	377.2	35.8
30°-40°	205.7	19.5
40°-50°	41.1	3.9
50°-60°	5.9	0.6
60°-70°	0.7	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	800.5	75.9
0°-40°	1006.2	95.5
0°-60°	1053.2	99.9
0°-90°	1054.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1054.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1279	
5°	1210	115
15°	1112	309
25°	847	377
35°	323	206
45°	47	41
55°	4	6
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P494951

CATALOG NUMBER: LDA2B108035R60D010 2LBD1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1279.3
1°	1273.4
2°	1262.2
3°	1247.2
4°	1225.9
5°	1209.8
6°	1201.3
7°	1191.1
8°	1183.1
9°	1179.4
10°	1170.8
11°	1161.2
12°	1152.7
13°	1142.5
14°	1127.6
15°	1111.6
16°	1091.3
17°	1063.0
18°	1044.8
19°	1015.4
20°	988.7
21°	964.1
22.5°	923.0
23°	905.9
24°	879.7
25°	846.6
26°	804.4
27°	760.1
28°	709.3
29°	661.3
30°	605.2
32.5°	464.2
35°	323.2
37.5°	202.4
40°	113.8
42.5°	71.0
45°	47.0
47.5°	32.0
50°	20.8
52.5°	10.7
55°	3.7
57.5°	1.6
60°	1.1
62.5°	1.1
65°	0.5



TEST NUMBER: P494951

CATALOG NUMBER: LDA2B108035R60D010 2LBD1LI

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.5
70°	0.5
72.5°	0.5
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)