

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P495016

Luminaire Tested: **LDA2B108035R70D010 2LBDLC1MW**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P495016
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-81)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B108035R70D010 2LBDLC1MW
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 3500K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1047.5 lumens
Efficiency: N/A
Efficacy: 104.7 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 10
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P495016

CATALOG NUMBER: LDA2B108035R70D010 2LBDLC1MW

Luminous Intensity Polar Plot





TEST NUMBER: P495016

CATALOG NUMBER: LDA2B108035R70D010 2LBDLC1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97	96	94	93
2	107	102	97	94	105	100	96	93	97	93	91		94	91	89		91	89	87	85
3	101	94	89	84	99	93	88	84	90	86	82		87	84	81		85	82	80	78
4	95	87	81	76	93	86	80	76	84	79	75		82	77	74		80	76	73	72
5	90	81	74	70	88	80	74	69	78	73	69		76	72	68		74	71	67	66
6	85	75	68	64	83	74	68	63	72	67	63		71	66	63		70	65	62	61
7	80	70	63	59	78	69	63	58	68	62	58		66	61	58		65	61	57	56
8	75	65	58	54	74	64	58	54	63	58	54		62	57	53		61	57	53	52
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57	53	49	48
10	68	57	51	46	66	57	50	46	56	50	46		55	50	46		54	49	46	45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	414671
5°	412293
10°	409545
15°	401922
20°	387416
25°	370876
30°	353319
35°	291505
40°	189476
45°	99006
50°	46052
55°	16859
60°	1677
65°	1401
70°	865
75°	1144
80°	0
85°	0



TEST NUMBER: P495016

CATALOG NUMBER: LDA2B108035R70D010 2LBDLC1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.7	7.5
10°-20°	221.1	21.1
20°-30°	313.9	30.0
30°-40°	293.5	28.0
40°-50°	118.0	11.3
50°-60°	20.6	2.0
60°-70°	1.0	0.1
70°-80°	0.6	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	613.7	58.6
0°-40°	907.2	86.6
0°-60°	1045.9	99.8
0°-90°	1047.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1047.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	840	
5°	832	79
15°	787	221
25°	681	314
35°	484	293
45°	142	118
55°	20	21
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P495016

CATALOG NUMBER: LDA2B108035R70D010 2LBDLC1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	840.5
1°	841.7
2°	840.0
3°	836.5
4°	834.8
5°	832.5
6°	823.2
7°	826.1
8°	818.0
9°	816.3
10°	817.5
11°	810.0
12°	808.2
13°	799.0
14°	795.5
15°	786.9
16°	781.7
17°	771.3
18°	759.2
19°	752.3
20°	737.9
21°	726.9
22.5°	706.7
23°	701.5
24°	691.7
25°	681.3
26°	673.2
27°	661.7
28°	650.2
29°	636.3
30°	620.2
32.5°	563.6
35°	484.0
37.5°	390.0
40°	294.2
42.5°	210.0
45°	141.9
47.5°	93.5
50°	60.0
52.5°	37.5
55°	19.6
57.5°	6.3
60°	1.7
62.5°	1.2
65°	1.2



TEST NUMBER: P495016

CATALOG NUMBER: LDA2B108035R70D010 2LBDLC1MW

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.6
70°	0.6
72.5°	0.6
75°	0.6
77.5°	0.6
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)