

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P278583

Luminaire Tested: **LDA2B108040D010 EU2B10NFL258040 2LBAD1WH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P278583
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B108040D010 EU2B10NFL258040 2LBAD1WH
Description: PORTFOLIO 2IN ADJ 1000 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC
AND 2in ADJ spun Refl, Self-Flanged, WH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1192.7 lumens
Efficiency: N/A
Efficacy: 119.3 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P278583

CATALOG NUMBER: LDA2B108040D010 EU2B10NFL258040 2LBAD1WH

Luminous Intensity Polar Plot





TEST NUMBER: P278583

CATALOG NUMBER: LDA2B108040D010 EU2B10NFL258040 2LBAD1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	115	113	111	110	113	111	109	108	107	106	105	103	102	102	100	99	99	97																																				
2	112	108	105	103	110	107	104	102	103	101	100	101	99	98	98	97	96	94																																				
3	108	104	100	98	107	103	99	97	100	98	95	98	96	94	96	94	93	91																																				
4	105	100	96	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89																																				
5	102	97	93	90	101	96	92	90	94	91	89	93	90	88	92	89	87	86																																				
6	100	94	90	87	98	93	89	87	92	89	86	91	88	86	89	87	85	84																																				
7	97	91	87	84	96	90	87	84	89	86	84	88	85	83	87	85	83	82																																				
8	95	88	85	82	94	88	84	82	87	84	81	86	83	81	85	83	81	80																																				
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78																																				
10	90	84	80	78	90	84	80	78	83	80	77	82	79	77	82	79	77	76																																				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3052676
5°	2815327
10°	1897184
15°	935365
20°	399544
25°	157049
30°	61868
35°	27103
40°	13010
45°	6279
50°	3454
55°	1892
60°	1085
65°	700
70°	865
75°	0
80°	0
85°	0



TEST NUMBER: P278583

CATALOG NUMBER: LDA2B108040D010 EU2B10NFL258040 2LBAD1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	481.5	40.4
10°-20°	518.6	43.5
20°-30°	149.7	12.6
30°-40°	31.6	2.6
40°-50°	7.8	0.7
50°-60°	2.2	0.2
60°-70°	0.8	0.1
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1149.9	96.4
0°-40°	1181.5	99.1
0°-60°	1191.5	99.9
0°-90°	1192.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1192.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6188	
5°	5685	482
15°	1831	519
25°	288	150
35°	45	32
45°	9	8
55°	2	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P278583

CATALOG NUMBER: LDA2B108040D010 EU2B10NFL258040 2LBAD1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	6187.5
1°	6148.7
2°	6082.9
3°	5994.1
4°	5868.1
5°	5684.7
6°	5437.2
7°	5114.4
8°	4717.3
9°	4254.4
10°	3787.0
11°	3314.5
12°	2868.5
13°	2472.5
14°	2124.4
15°	1831.3
17.5°	1210.4
20°	761.0
22.5°	468.0
25°	288.5
27.5°	176.0
30°	108.6
32.5°	68.6
35°	45.0
37.5°	29.8
40°	20.2
42.5°	14.1
45°	9.0
47.5°	5.6
50°	4.5
52.5°	3.4
55°	2.2
57.5°	1.7
60°	1.1
62.5°	1.1
65°	0.6
67.5°	0.6
70°	0.6
72.5°	0.6
75°	0.0
77.5°	0.6
80°	0.0
82.5°	0.0



TEST NUMBER: P278583

CATALOG NUMBER: LDA2B108040D010 EU2B10NFL258040 2LBAD1WH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)