

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P278061

Luminaire Tested: **LDA2B109727D010 EU2B10SP159727 2LBAD1B**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P278061
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-1)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B109727D010 EU2B10SP159727 2LBAD1B
Description: PORTFOLIO 2IN ADJ 1000 LUMEN LED LUMINAIRE WITH SPOT OPTIC AND 2in
ADJ spun Refl, Self-Flanged, B
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 752.6 lumens
Efficiency: N/A
Efficacy: 75.3 lumens/watt
Spacing Criteria (0/90/45): 0.28 / 0.28 / 0.28
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P278061

CATALOG NUMBER: LDA2B109727D010 EU2B10SP159727 2LBAD1B

Luminous Intensity Polar Plot





TEST NUMBER: P278061

CATALOG NUMBER: LDA2B109727D010 EU2B10SP159727 2LBAD1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	116	114	112	110	113	112	110	109	108	106	105	104	103	102	101	100	99	98			98
2	112	109	107	104	110	108	105	103	105	103	101	102	100	99	99	98	97	96			96
3	109	105	102	100	108	104	101	99	102	99	98	100	98	96	97	96	95	93			93
4	107	102	99	96	105	101	98	96	99	97	95	98	95	94	96	94	93	92			92
5	104	99	96	93	103	99	95	93	97	94	92	96	93	91	94	92	91	90			90
6	102	97	93	91	101	96	93	91	95	92	90	94	91	89	93	91	89	88			88
7	100	95	91	89	99	94	91	88	93	90	88	92	90	88	91	89	87	86			86
8	98	93	89	87	97	92	89	87	91	88	86	90	88	86	90	87	86	85			85
9	96	91	87	85	95	90	87	85	90	87	85	89	86	84	88	86	84	83			83
10	94	89	86	83	94	89	85	83	88	85	83	87	85	83	87	85	83	82			82

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3400101
5°	2710780
10°	1176885
15°	406621
20°	166695
25°	75286
30°	30307
35°	14093
40°	7664
45°	2861
50°	1689
55°	1290
60°	691
65°	467
70°	577
75°	0
80°	0
85°	0



TEST NUMBER: P278061

CATALOG NUMBER: LDA2B109727D010 EU2B10SP159727 2LBAD1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	413.7	55.0
10°-20°	248.4	33.0
20°-30°	68.4	9.1
30°-40°	16.3	2.2
40°-50°	4.0	0.5
50°-60°	1.3	0.2
60°-70°	0.5	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	730.5	97.1
0°-40°	746.8	99.2
0°-60°	752.1	99.9
0°-90°	752.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	752.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6892	
5°	5474	414
15°	796	248
25°	138	68
35°	23	16
45°	4	4
55°	2	1
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P278061

CATALOG NUMBER: LDA2B109727D010 EU2B10SP159727 2LBAD1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	6891.7
1°	6815.5
2°	6632.9
3°	6354.4
4°	5961.4
5°	5473.6
6°	4877.9
7°	4225.4
8°	3539.7
9°	2909.1
10°	2349.2
11°	1875.1
12°	1492.5
13°	1203.6
14°	973.8
15°	796.1
17.5°	494.1
20°	317.5
22.5°	208.2
25°	138.3
27.5°	88.9
30°	53.2
32.5°	33.5
35°	23.4
37.5°	17.1
40°	11.9
42.5°	7.1
45°	4.1
47.5°	3.0
50°	2.2
52.5°	1.9
55°	1.5
57.5°	1.1
60°	0.7
62.5°	0.7
65°	0.4
67.5°	0.4
70°	0.4
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P278061

CATALOG NUMBER: LDA2B109727D010 EU2B10SP159727 2LBAD1B

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)