

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P278588

Luminaire Tested: **LDA2B108040D010 EU2B10NFL258040 2LBALD1MW**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P278588  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA2B108040D010 EU2B10NFL258040 2LBALD1MW  
Description: PORTFOLIO 2IN ADJ 1000 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC  
AND 2in ADJ spun Refl w/lens Self-Flanged, MW  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1112.4 lumens  
Efficiency: N/A  
Efficacy: 111.2 lumens/watt  
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P278588

CATALOG NUMBER: LDA2B108040D010 EU2B10NFL258040 2LBALD1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P278588

CATALOG NUMBER: LDA2B108040D010 EU2B10NFL258040 2LBALD1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	115	113	111	110	113	111	109	108	107	106	105	103	102	102	100	99	99	97			97																
2	112	108	105	103	110	107	104	102	103	101	100	101	99	98	98	97	96	94			94																
3	108	104	100	98	107	103	99	97	100	98	95	98	96	94	96	94	93	91			91																
4	105	100	96	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89			89																
5	102	97	93	90	101	96	92	90	94	91	89	93	90	88	92	89	87	86			86																
6	100	94	90	87	98	93	89	87	92	89	86	91	88	86	89	87	85	84			84																
7	97	91	87	84	96	90	87	84	89	86	84	88	85	83	87	85	83	82			82																
8	95	88	85	82	94	88	84	82	87	84	81	86	83	81	85	83	81	80			80																
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78			78																
10	90	84	80	78	90	84	80	78	83	80	78	82	79	77	82	79	77	76			76																

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	2847388
5°	2625994
10°	1769586
15°	872490
20°	372662
25°	146488
30°	57709
35°	25296
40°	12172
45°	5861
50°	3224
55°	1806
60°	987
65°	584
70°	721
75°	0
80°	0
85°	0



TEST NUMBER: P278588

CATALOG NUMBER: LDA2B108040D010 EU2B10NFL258040 2LBALD1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	449.2	40.4
10°-20°	483.7	43.5
20°-30°	139.7	12.6
30°-40°	29.5	2.7
40°-50°	7.2	0.7
50°-60°	2.1	0.2
60°-70°	0.7	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1072.5	96.4
0°-40°	1102.0	99.1
0°-60°	1111.4	99.9
0°-90°	1112.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1112.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5771	
5°	5302	449
15°	1708	484
25°	269	140
35°	42	29
45°	8	7
55°	2	2
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P278588

CATALOG NUMBER: LDA2B108040D010 EU2B10NFL258040 2LBALD1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	5771.4
1°	5735.2
2°	5673.8
3°	5591.0
4°	5473.4
5°	5302.4
6°	5071.6
7°	4770.4
8°	4400.1
9°	3968.3
10°	3532.3
11°	3091.6
12°	2675.6
13°	2306.3
14°	1981.5
15°	1708.2
17.5°	1129.0
20°	709.8
22.5°	436.5
25°	269.1
27.5°	164.2
30°	101.3
32.5°	64.0
35°	42.0
37.5°	27.8
40°	18.9
42.5°	13.1
45°	8.4
47.5°	5.2
50°	4.2
52.5°	3.1
55°	2.1
57.5°	1.6
60°	1.0
62.5°	1.0
65°	0.5
67.5°	0.5
70°	0.5
72.5°	0.5
75°	0.0
77.5°	0.5
80°	0.0
82.5°	0.0



TEST NUMBER: P278588

CATALOG NUMBER: LDA2B108040D010 EU2B10NFL258040 2LBALD1MW

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)