

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P496745

Luminaire Tested: **LDA2B109727R20D010 2LBD1B-30DEG TILT**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P496745  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-2)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/8/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B109727R20D010 2LBD1B-30DEG TILT  
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 97 CRI LEDS AND 2700K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 479.3 lumens  
Efficiency: N/A  
Efficacy: 47.9 lumens/watt  
Spacing Criteria (0/90/45): 2.56 / 0.56 / 1.2  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P496745

CATALOG NUMBER: LDA2B109727R20D010 2LBD1B-30DEG TILT

### Luminous Intensity Polar Plot



— 0°-180°    - - 45°-225°    - - - 90°-270°



TEST NUMBER: P496745

CATALOG NUMBER: LDA2B109727R20D010 2LBD1B-30DEG TILT

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91					91			
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82					82			
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74					74			
4	92	83	76	71	90	82	75	70	79	74	70	77	73	69	75	71	68	66					66			
5	86	75	68	63	84	74	68	63	73	67	62	71	66	62	69	65	61	59					59			
6	80	69	62	56	78	68	61	56	66	60	56	65	59	55	63	59	55	53					53			
7	74	63	55	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48					48			
8	69	57	50	45	68	57	50	45	56	49	45	54	49	44	53	48	44	43					43			
9	64	53	45	40	63	52	45	40	51	45	40	50	44	40	49	44	40	38					38			
10	60	48	41	36	59	48	41	36	47	41	36	46	40	36	45	40	36	34					34			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	7598	7598	7598
5°	14560	6735	4903
10°	34818	5911	3306
15°	202723	4699	1328
20°	1011250	2888	368
25°	1843871	980	0
30°	2162696	0	0
35°	1892917	0	0
40°	1397885	0	0
45°	503823	0	0
50°	104922	0	0
55°	23998	344	0
60°	7598	395	0
65°	1751	817	0
70°	0	1010	577
75°	0	1334	0
80°	0	1989	0
85°	0	3962	0



TEST NUMBER: P496745

CATALOG NUMBER: LDA2B109727R20D010 2LBD1B-30DEG TILT

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1.7	0.4
10°-20°	26.3	5.5
20°-30°	177.5	37.0
30°-40°	207.4	43.3
40°-50°	60.5	12.6
50°-60°	4.0	0.8
60°-70°	0.7	0.2
70°-80°	0.6	0.1
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	205.6	42.9
0°-40°	413.0	86.2
0°-60°	477.5	99.6
0°-90°	479.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	479.3	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	15	15	15	15	15	
5°	29	21	14	11	10	4
15°	397	45	9	5	3	207
25°	3387	70	2	0	0	1500
35°	3143	38	0	0	0	1931
45°	722	8	0	0	0	665
55°	28	2	0	0	0	36
65°	2	1	1	1	0	2
75°	0	1	1	1	0	0
85°	0	1	1	1	0	0
90°	0	0	0	0	0	



TEST NUMBER: P496745

CATALOG NUMBER: LDA2B109727R20D010 2LBD1B-30DEG TILT

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	15.4	15.4	15.4	15.4	15.4	15.4	15.4	15.4	15.4
2.5°	19.8	19.8	17.6	15.8	14.3	13.6	13.2	12.5	12.1
5°	29.4	25.7	21.3	16.5	13.6	12.5	11.4	10.3	9.9
7.5°	43.0	37.5	25.7	16.9	12.9	11.0	9.9	8.8	8.1
10°	69.5	54.0	31.6	16.9	11.8	9.6	8.1	7.0	6.6
12.5°	128.3	82.7	37.9	16.5	10.7	8.1	6.2	5.5	4.4
15°	396.9	171.3	44.8	15.8	9.2	6.2	4.8	2.9	2.6
17.5°	1026.4	399.8	50.0	14.0	7.3	4.4	2.2	1.8	1.8
20°	1926.1	725.1	57.3	12.1	5.5	2.9	1.5	1.1	0.7
21°	2197.3	887.1	61.0	11.4	4.8	1.8	1.1	0.4	0.4
22°	2618.8	1063.9	63.9	10.7	4.0	1.1	0.7	0.4	0.0
23°	2919.0	1176.7	66.9	9.6	2.9	1.1	0.4	0.0	0.0
24°	3219.3	1320.4	68.7	8.8	2.6	0.7	0.4	0.0	0.0
25°	3387.2	1440.2	69.5	8.1	1.8	0.4	0.0	0.0	0.0
26°	3525.4	1520.3	69.8	7.3	1.1	0.0	0.0	0.0	0.0
27°	3643.8	1613.3	69.1	6.6	1.1	0.0	0.0	0.0	0.0
28°	3711.0	1628.8	68.0	5.9	0.4	0.0	0.0	0.0	0.0
29°	3740.0	1610.0	64.7	5.1	0.4	0.0	0.0	0.0	0.0
30°	3796.3	1592.4	61.4	4.8	0.0	0.0	0.0	0.0	0.0
31°	3744.5	1533.9	57.3	4.0	0.0	0.0	0.0	0.0	0.0
32°	3541.6	1484.7	52.6	3.3	0.0	0.0	0.0	0.0	0.0
33°	3481.0	1383.6	47.4	2.9	0.0	0.0	0.0	0.0	0.0
34°	3366.7	1233.3	43.0	2.6	0.0	0.0	0.0	0.0	0.0
35°	3142.9	1109.1	37.5	2.2	0.0	0.0	0.0	0.0	0.0
36°	2986.7	967.3	32.7	1.8	0.0	0.0	0.0	0.0	0.0
37°	2823.1	843.4	29.0	1.5	0.0	0.0	0.0	0.0	0.0
38°	2619.9	713.3	24.6	1.1	0.0	0.0	0.0	0.0	0.0
39°	2383.2	589.5	20.9	1.1	0.0	0.0	0.0	0.0	0.0
40°	2170.5	475.2	18.0	0.7	0.0	0.0	0.0	0.0	0.0
42.5°	1339.5	271.2	10.7	0.7	0.0	0.0	0.0	0.0	0.0
45°	722.1	164.6	7.7	0.4	0.0	0.0	0.0	0.0	0.0
47.5°	332.6	76.8	5.5	0.4	0.0	0.0	0.0	0.0	0.0
50°	136.7	34.2	4.0	0.0	0.0	0.0	0.0	0.0	0.0
52.5°	49.2	19.1	2.6	0.0	0.0	0.4	0.0	0.0	0.0
55°	27.9	11.0	1.5	0.4	0.4	0.4	0.4	0.0	0.0
57.5°	13.2	6.2	0.4	0.4	0.4	0.4	0.4	0.0	0.0
60°	7.7	3.3	0.4	0.4	0.4	0.7	0.4	0.0	0.0
62.5°	3.7	1.1	0.4	0.7	0.7	0.7	0.7	0.4	0.0
65°	1.5	0.4	0.7	0.7	0.7	1.1	0.7	0.4	0.0
67.5°	0.4	0.4	0.7	0.7	0.7	1.1	0.7	0.4	0.4
70°	0.0	0.4	0.7	0.7	0.7	1.1	0.7	0.4	0.4
72.5°	0.0	0.4	0.7	0.7	0.7	1.1	0.7	0.4	0.4
75°	0.0	0.4	0.7	0.7	0.7	0.7	0.7	0.4	0.0
77.5°	0.0	0.4	0.7	0.7	0.7	0.7	0.7	0.4	0.0
80°	0.0	0.4	0.7	0.7	0.7	0.7	0.7	0.4	0.0



TEST NUMBER: P496745

CATALOG NUMBER: LDA2B109727R20D010 2LBD1B-30DEG TILT

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
82.5°	0.0	0.4	0.7	0.7	0.7	0.7	0.7	0.4	0.0
85°	0.0	0.4	0.7	0.7	0.7	0.7	0.7	0.4	0.0
87.5°	0.0	0.4	0.7	0.7	0.7	0.7	0.4	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)