

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P277998

Luminaire Tested: **LDA2B108040D010 EU2B10SP158040 2LBAD1WMH**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P277998  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-1)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA2B108040D010 EU2B10SP158040 2LBAD1WMH  
Description: PORTFOLIO 2IN ADJ 1000 LUMEN LED LUMINAIRE WITH SPOT OPTIC AND 2in  
ADJ spun Refl, Self-Flanged, WMH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1138.7 lumens  
Efficiency: N/A  
Efficacy: 113.9 lumens/watt  
Spacing Criteria (0/90/45): 0.28 / 0.28 / 0.28  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P277998

CATALOG NUMBER: LDA2B108040D010 EU2B10SP158040 2LBAD1WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P277998

CATALOG NUMBER: LDA2B108040D010 EU2B10SP158040 2LBAD1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	116	114	112	110	113	112	110	109	108	106	105	104	103	102	101	100	99	98
2	112	109	107	104	110	108	105	103	105	103	101	102	100	99	99	98	97	96
3	109	105	102	100	108	104	101	99	102	99	98	100	98	96	97	96	95	93
4	107	102	99	96	105	101	98	96	99	97	95	98	95	94	96	94	93	92
5	104	99	96	93	103	99	95	93	97	94	92	96	93	91	94	92	91	90
6	102	97	93	91	101	96	93	91	95	92	90	94	91	89	93	91	89	88
7	100	95	91	89	99	94	91	88	93	90	88	92	90	88	91	89	87	86
8	98	93	89	87	97	92	89	87	91	88	86	90	88	86	90	87	86	85
9	96	91	87	85	95	90	87	85	90	87	85	89	86	84	88	86	84	83
10	94	89	86	83	94	89	85	83	88	85	83	87	85	83	87	85	83	82

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	5144037
5°	4101135
10°	1780507
15°	615166
20°	252222
25°	113935
30°	45803
35°	21321
40°	11593
45°	4326
50°	2610
55°	1978
60°	1085
65°	700
70°	865
75°	0
80°	0
85°	0



TEST NUMBER: P277998

CATALOG NUMBER: LDA2B108040D010 EU2B10SP158040 2LBAD1WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	625.8	55.0
10°-20°	375.9	33.0
20°-30°	103.5	9.1
30°-40°	24.6	2.2
40°-50°	6.1	0.5
50°-60°	2.0	0.2
60°-70°	0.8	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1105.2	97.1
0°-40°	1129.7	99.2
0°-60°	1137.8	99.9
0°-90°	1138.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1138.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	10426	
5°	8281	626
15°	1204	376
25°	209	103
35°	35	25
45°	6	6
55°	2	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P277998

CATALOG NUMBER: LDA2B108040D010 EU2B10SP158040 2LBAD1WMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	10426.5
1°	10311.2
2°	10035.0
3°	9613.6
4°	9019.0
5°	8281.0
6°	7379.8
7°	6392.6
8°	5355.3
9°	4401.2
10°	3554.1
11°	2836.8
12°	2258.0
13°	1820.9
14°	1473.3
15°	1204.4
17.5°	747.6
20°	480.4
22.5°	315.0
25°	209.3
27.5°	134.4
30°	80.4
32.5°	50.6
35°	35.4
37.5°	25.9
40°	18.0
42.5°	10.7
45°	6.2
47.5°	4.5
50°	3.4
52.5°	2.8
55°	2.3
57.5°	1.7
60°	1.1
62.5°	1.1
65°	0.6
67.5°	0.6
70°	0.6
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P277998

CATALOG NUMBER: LDA2B108040D010 EU2B10SP158040 2LBAD1WMH

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)