

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P495098

Luminaire Tested: **LDA2B108040R30D010 2LBPIN1H**

Issue Date: 3/12/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P495098  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-14)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/12/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B108040R30D010 2LBPIN1H  
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 4000K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 903.2 lumens  
Efficiency: N/A  
Efficacy: 90.3 lumens/watt  
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.46  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P495098

CATALOG NUMBER: LDA2B108040R30D010 2LBPIN1H

### Luminous Intensity Polar Plot





TEST NUMBER: P495098

CATALOG NUMBER: LDA2B108040R30D010 2LBPIN1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97
2	111	108	105	102	109	106	103	101	103	101	99	100	98	97	97	96	95	93
3	108	103	100	97	106	102	99	96	99	97	94	97	95	93	95	93	92	90
4	104	99	95	92	103	98	94	92	96	93	91	94	92	90	92	90	89	87
5	101	95	91	88	100	95	91	88	93	90	87	91	89	86	90	88	86	85
6	98	92	88	85	97	91	88	85	90	87	84	89	86	84	88	85	83	82
7	96	89	85	82	95	89	85	82	87	84	81	86	83	81	85	83	81	80
8	93	86	82	79	92	86	82	79	85	81	79	84	81	79	83	81	78	77
9	90	84	80	77	90	83	80	77	83	79	77	82	79	76	81	78	76	75
10	88	81	77	75	87	81	77	75	80	77	75	80	77	74	79	76	74	73

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1750398
5°	1668980
10°	1353478
15°	827389
20°	361532
25°	135275
30°	56057
35°	26199
40°	12172
45°	5931
50°	3300
55°	1204
60°	493
65°	584
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P495098

CATALOG NUMBER: LDA2B108040R30D010 2LBPIN1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	300.6	33.3
10°-20°	434.0	48.1
20°-30°	129.5	14.3
30°-40°	29.8	3.3
40°-50°	7.3	0.8
50°-60°	1.6	0.2
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	864.2	95.7
0°-40°	894.0	99.0
0°-60°	902.9	100.0
0°-90°	903.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	903.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3548	
5°	3370	301
15°	1620	434
25°	248	130
35°	44	30
45°	8	7
55°	1	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P495098

CATALOG NUMBER: LDA2B108040R30D010 2LBPIN1H

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3547.9
1°	3539.9
2°	3503.9
3°	3479.8
4°	3434.8
5°	3370.0
6°	3281.5
7°	3175.9
8°	3041.5
9°	2877.8
10°	2701.7
11°	2513.4
12°	2299.5
13°	2069.5
14°	1850.9
15°	1619.9
16°	1396.5
17°	1176.5
18°	999.0
19°	826.8
20°	688.6
21°	558.0
22.5°	413.6
23°	372.9
24°	305.2
25°	248.5
26°	204.0
27°	169.9
28°	140.1
29°	117.4
30°	98.4
32.5°	64.4
35°	43.5
37.5°	28.9
40°	18.9
42.5°	12.3
45°	8.5
47.5°	6.2
50°	4.3
52.5°	2.8
55°	1.4
57.5°	0.9
60°	0.5
62.5°	0.5
65°	0.5



TEST NUMBER: P495098

CATALOG NUMBER: LDA2B108040R30D010 2LBPIN1H

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)