

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P496870

Luminaire Tested: **LDA2B109727R45D010 2LBD1GPH**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P496870
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-40)
Test Lab: INNOVATION CENTER
Issue Date: 3/8/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B109727R45D010 2LBD1GPH
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 97 CRI LEDS AND 2700K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 759.6 lumens
Efficiency: N/A
Efficacy: 76.0 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 0.71 / 0.65
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 10
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P496870
CATALOG NUMBER: LDA2B109727R45D010 2LBD1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P496870

CATALOG NUMBER: LDA2B109727R45D010 2LBD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95
2	110	106	102	99	108	104	101	98	101	98	96	98	96	94	95	94	92	91
3	105	100	96	93	104	99	95	92	96	93	90	94	91	89	92	90	88	86
4	101	95	90	87	100	94	90	86	92	88	85	90	87	84	88	86	83	82
5	97	90	86	82	96	90	85	82	88	84	81	86	83	80	85	82	80	78
6	94	86	81	78	92	86	81	77	84	80	77	83	79	76	82	78	76	75
7	90	82	77	74	89	82	77	74	81	76	73	80	76	73	78	75	73	71
8	87	79	74	70	86	78	74	70	77	73	70	76	73	70	76	72	70	68
9	84	76	71	67	83	75	70	67	74	70	67	73	70	67	73	69	67	66
10	81	73	68	65	80	72	68	64	71	67	64	71	67	64	70	67	64	63

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	753906
5°	742374
10°	692795
15°	604593
20°	462284
25°	268481
30°	113880
35°	47159
40°	20802
45°	10745
50°	5373
55°	1290
60°	691
65°	467
70°	577
75°	0
80°	0
85°	0



TEST NUMBER: P496870

CATALOG NUMBER: LDA2B109727R45D010 2LBD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	139.5	18.4
10°-20°	322.8	42.5
20°-30°	225.7	29.7
30°-40°	55.9	7.4
40°-50°	12.9	1.7
50°-60°	2.1	0.3
60°-70°	0.4	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	688.1	90.6
0°-40°	743.9	97.9
0°-60°	759.0	99.9
0°-90°	759.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	759.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1528	
5°	1499	139
15°	1184	323
25°	493	226
35°	78	56
45°	15	13
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P496870

CATALOG NUMBER: LDA2B109727R45D010 2LBD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1528.1
1°	1524.8
2°	1524.0
3°	1519.2
4°	1505.6
5°	1499.0
6°	1485.4
7°	1466.0
8°	1442.1
9°	1417.4
10°	1382.9
11°	1354.6
12°	1320.1
13°	1275.2
14°	1229.7
15°	1183.7
16°	1133.0
17°	1072.7
18°	1011.7
19°	948.9
20°	880.5
21°	798.6
22.5°	692.4
23°	648.6
24°	570.0
25°	493.2
26°	421.2
27°	353.9
28°	294.7
29°	243.3
30°	199.9
32.5°	123.1
35°	78.3
37.5°	50.7
40°	32.3
42.5°	22.1
45°	15.4
47.5°	11.0
50°	7.0
52.5°	3.7
55°	1.5
57.5°	0.7
60°	0.7
62.5°	0.4
65°	0.4



TEST NUMBER: P496870

CATALOG NUMBER: LDA2B109727R45D010 2LBD1GPH

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)