

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P495162

Luminaire Tested: **LDA2B108040R45D010 2LBDLC1MMS**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P495162
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-42)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B108040R45D010 2LBDLC1MMS
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 4000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1149.2 lumens
Efficiency: N/A
Efficacy: 114.9 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.65
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 10
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P495162

CATALOG NUMBER: LDA2B108040R45D010 2LBDLC1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P495162

CATALOG NUMBER: LDA2B108040R45D010 2LBDLC1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	110	105	102	99	108	104	101	98	101	98	96		98	96	94		95	93	92	90
3	105	100	96	92	103	98	95	91	96	93	90		94	91	89		91	89	87	86
4	101	95	90	86	99	94	89	86	91	88	85		90	86	84		88	85	83	82
5	97	90	85	81	95	89	84	81	87	83	80		86	82	80		84	81	79	78
6	93	86	81	77	92	85	80	77	84	79	76		82	79	76		81	78	75	74
7	90	82	77	73	88	81	76	73	80	76	73		79	75	72		78	74	72	71
8	86	78	73	70	85	78	73	70	77	72	69		76	72	69		75	71	69	68
9	83	75	70	66	82	74	70	66	74	69	66		73	69	66		72	68	66	65
10	80	72	67	64	79	71	67	64	71	66	63		70	66	63		69	66	63	62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1139024
5°	1113908
10°	1033457
15°	881326
20°	663526
25°	399999
30°	192895
35°	87452
40°	40252
45°	20792
50°	10976
55°	4129
60°	1184
65°	700
70°	865
75°	0
80°	0
85°	0



TEST NUMBER: P495162

CATALOG NUMBER: LDA2B108040R45D010 2LBDLC1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	209.1	18.2
10°-20°	471.2	41.0
20°-30°	336.6	29.3
30°-40°	100.9	8.8
40°-50°	25.0	2.2
50°-60°	5.2	0.5
60°-70°	0.8	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1017.0	88.5
0°-40°	1117.9	97.3
0°-60°	1148.2	99.9
0°-90°	1149.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1149.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2309	
5°	2249	209
15°	1726	471
25°	735	337
35°	145	101
45°	30	25
55°	5	5
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P495162

CATALOG NUMBER: LDA2B108040R45D010 2LBDLC1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	2308.7
1°	2312.8
2°	2307.5
3°	2287.8
4°	2273.5
5°	2249.2
6°	2224.8
7°	2198.6
8°	2155.7
9°	2115.3
10°	2062.9
11°	2010.6
12°	1944.5
13°	1873.7
14°	1807.7
15°	1725.5
16°	1645.2
17°	1554.2
18°	1467.9
19°	1362.0
20°	1263.8
21°	1154.9
22.5°	992.5
23°	937.7
24°	831.2
25°	734.8
26°	638.5
27°	550.4
28°	468.3
29°	401.0
30°	338.6
32.5°	222.5
35°	145.2
37.5°	95.2
40°	62.5
42.5°	42.2
45°	29.8
47.5°	21.4
50°	14.3
52.5°	8.9
55°	4.8
57.5°	2.4
60°	1.2
62.5°	1.2
65°	0.6



TEST NUMBER: P495162

CATALOG NUMBER: LDA2B108040R45D010 2LBDLC1MMS

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.6
70°	0.6
72.5°	0.6
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)