

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P496946

Luminaire Tested: **LDA2B109727R70D010 2LBD1WHH**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P496946
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-79)
Test Lab: INNOVATION CENTER
Issue Date: 3/8/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B109727R70D010 2LBD1WHH
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 97 CRI LEDS AND 2700K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 720.6 lumens
Efficiency: N/A
Efficacy: 72.1 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.09
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 10
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P496946

CATALOG NUMBER: LDA2B109727R70D010 2LBD1WHH

Luminous Intensity Polar Plot





TEST NUMBER: P496946

CATALOG NUMBER: LDA2B109727R70D010 2LBD1WHH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	85	82	80	78
4	95	87	81	77	93	86	81	76	84	79	75	82	78	74	80	76	74	72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61
7	80	70	63	59	79	69	63	59	68	62	58	67	62	58	66	61	58	56
8	76	65	59	54	74	65	59	54	64	58	54	62	57	54	61	57	54	52
9	71	61	55	50	70	61	54	50	60	54	50	59	54	50	58	53	50	48
10	68	57	51	47	67	57	51	47	56	50	47	55	50	46	54	50	46	45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	281562
5°	278477
10°	277088
15°	276120
20°	266240
25°	255253
30°	252712
35°	215798
40°	134668
45°	62306
50°	22566
55°	1548
60°	691
65°	817
70°	577
75°	762
80°	0
85°	0



TEST NUMBER: P496946

CATALOG NUMBER: LDA2B109727R70D010 2LBD1WHH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.3	7.4
10°-20°	151.4	21.0
20°-30°	217.7	30.2
30°-40°	214.6	29.8
40°-50°	76.5	10.6
50°-60°	6.3	0.9
60°-70°	0.6	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	422.4	58.6
0°-40°	637.0	88.4
0°-60°	719.8	99.9
0°-90°	720.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	720.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	571	
5°	562	53
15°	541	151
25°	469	218
35°	358	215
45°	89	76
55°	2	6
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P496946

CATALOG NUMBER: LDA2B109727R70D010 2LBD1WHH

CANDELA DISTRIBUTION (FULL):

0°	
0°	570.7
1°	570.7
2°	569.6
3°	570.0
4°	565.2
5°	562.3
6°	558.2
7°	556.8
8°	554.9
9°	554.6
10°	553.1
11°	551.2
12°	551.2
13°	547.9
14°	543.5
15°	540.6
16°	534.7
17°	531.4
18°	521.1
19°	514.1
20°	507.1
21°	498.0
22.5°	485.1
23°	480.0
24°	475.2
25°	468.9
26°	465.3
27°	459.0
28°	458.3
29°	451.7
30°	443.6
32.5°	412.3
35°	358.3
37.5°	288.1
40°	209.1
42.5°	143.0
45°	89.3
47.5°	53.3
50°	29.4
52.5°	11.0
55°	1.8
57.5°	1.1
60°	0.7
62.5°	0.7
65°	0.7



TEST NUMBER: P496946

CATALOG NUMBER: LDA2B109727R70D010 2LBD1WHH

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.4
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)