

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P495190

Luminaire Tested: **LDA2B108040R65D010 2LBD1LI**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P495190  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-66)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/8/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B108040R65D010 2LBD1LI  
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 4000K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1125.9 lumens  
Efficiency: N/A  
Efficacy: 112.6 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.95  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P495190  
CATALOG NUMBER: LDA2B108040R65D010 2LBD1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P495190

CATALOG NUMBER: LDA2B108040R65D010 2LBD1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75
5	92	83	78	73	90	82	77	73	81	76	72	79	75	72	77	74	71	69
6	87	78	72	68	86	77	72	67	76	71	67	74	70	66	73	69	66	65
7	83	73	67	63	81	73	67	63	71	66	62	70	65	62	69	65	62	60
8	78	69	63	58	77	68	62	58	67	62	58	66	61	58	65	61	58	56
9	75	65	59	55	73	64	58	54	63	58	54	62	58	54	61	57	54	53
10	71	61	55	51	70	61	55	51	60	55	51	59	54	51	58	54	51	49

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	611719
5°	562550
10°	537594
15°	516282
20°	475515
25°	440391
30°	403508
35°	296384
40°	140336
45°	46189
50°	14967
55°	1892
60°	1085
65°	700
70°	865
75°	0
80°	0
85°	0



TEST NUMBER: P495190

CATALOG NUMBER: LDA2B108040R65D010 2LBD1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	106.7	9.5
10°-20°	281.1	25.0
20°-30°	372.9	33.1
30°-40°	295.0	26.2
40°-50°	64.5	5.7
50°-60°	4.8	0.4
60°-70°	0.7	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	760.7	67.6
0°-40°	1055.7	93.8
0°-60°	1125.0	99.9
0°-90°	1125.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1125.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1240	
5°	1136	107
15°	1011	281
25°	809	373
35°	492	295
45°	66	64
55°	2	5
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P495190

CATALOG NUMBER: LDA2B108040R65D010 2LBD1LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1239.9
1°	1233.2
2°	1210.4
3°	1185.4
4°	1159.2
5°	1135.9
6°	1120.9
7°	1105.9
8°	1095.9
9°	1080.8
10°	1073.1
11°	1060.8
12°	1046.9
13°	1034.7
14°	1020.8
15°	1010.8
16°	985.2
17°	972.4
18°	951.3
19°	931.8
20°	905.7
21°	884.6
22.5°	856.8
23°	849.0
24°	827.9
25°	809.0
26°	797.3
27°	777.8
28°	758.9
29°	736.1
30°	708.3
32.5°	611.6
35°	492.1
37.5°	350.8
40°	217.9
42.5°	122.9
45°	66.2
47.5°	35.6
50°	19.5
52.5°	8.3
55°	2.2
57.5°	1.1
60°	1.1
62.5°	0.6
65°	0.6



TEST NUMBER: P495190

CATALOG NUMBER: LDA2B108040R65D010 2LBD1LI

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.6
70°	0.6
72.5°	0.6
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)