

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P314975

Luminaire Tested: **LDA2B10NFL8040D010 PIN1MMS**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P314975  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA2B10NFL8040D010 PIN1MMS  
Description: PORTFOLIO 2IN ADJ 1000 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC  
AND 2in Adj PinHole, Black oculus, matte metallic silver finish  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1033.1 lumens  
Efficiency: N/A  
Efficacy: 103.3 lumens/watt  
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P314975

CATALOG NUMBER: LDA2B10NFL8040D010 PIN1MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P314975

CATALOG NUMBER: LDA2B10NFL8040D010 PIN1MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |    |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |  |  |  |  |  |    |  |  |  |  |  |  |  |  |
|-----|----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|--|--|--|--|--|----|--|--|--|--|--|--|--|--|
| RF  | 20 |     |     |     |     |     |     |     |     | 20  |     |     |     |     |     |     |     |     | 20  |     |     |     |     |     |     |     |     | 20  |     |     |    |  |  |  |  |  | 20 |  |  |  |  |  |  |  |  |
| RC  | 80 |     |     |     |     |     |     |     |     | 50  |     |     |     |     |     |     |     |     | 30  |     |     |     |     |     |     |     |     | 10  |     |     |    |  |  |  |  |  | 0  |  |  |  |  |  |  |  |  |
| RW  | 70 | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 0   |    |  |  |  |  |  |    |  |  |  |  |  |  |  |  |
| RCR | 0  | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 100 | 100 | 100 | 100 | 100 | 100 | 100 | 100 | 100 | 100 |    |  |  |  |  |  |    |  |  |  |  |  |  |  |  |
|     | 1  | 115 | 113 | 111 | 110 | 113 | 111 | 109 | 108 | 107 | 106 | 105 | 103 | 102 | 102 | 100 | 99  | 99  | 97  | 97  | 97  | 97  | 97  | 97  | 97  | 97  | 97  | 97  | 97  | 97  |    |  |  |  |  |  |    |  |  |  |  |  |  |  |  |
|     | 2  | 112 | 108 | 105 | 103 | 110 | 107 | 104 | 102 | 103 | 101 | 100 | 101 | 99  | 98  | 98  | 97  | 96  | 94  | 94  | 94  | 94  | 94  | 94  | 94  | 94  | 94  | 94  | 94  | 94  |    |  |  |  |  |  |    |  |  |  |  |  |  |  |  |
|     | 3  | 108 | 104 | 100 | 98  | 107 | 103 | 99  | 97  | 100 | 98  | 95  | 98  | 96  | 94  | 96  | 94  | 93  | 91  | 91  | 91  | 91  | 91  | 91  | 91  | 91  | 91  | 91  | 91  | 91  |    |  |  |  |  |  |    |  |  |  |  |  |  |  |  |
|     | 4  | 105 | 100 | 96  | 94  | 104 | 99  | 96  | 93  | 97  | 94  | 92  | 95  | 93  | 91  | 94  | 92  | 90  | 89  | 89  | 89  | 89  | 89  | 89  | 89  | 89  | 89  | 89  | 89  | 89  |    |  |  |  |  |  |    |  |  |  |  |  |  |  |  |
|     | 5  | 102 | 97  | 93  | 90  | 101 | 96  | 92  | 90  | 94  | 91  | 89  | 93  | 90  | 88  | 92  | 89  | 87  | 86  | 86  | 86  | 86  | 86  | 86  | 86  | 86  | 86  | 86  | 86  | 86  |    |  |  |  |  |  |    |  |  |  |  |  |  |  |  |
|     | 6  | 100 | 94  | 90  | 87  | 98  | 93  | 89  | 87  | 92  | 89  | 86  | 91  | 88  | 86  | 89  | 87  | 85  | 84  | 84  | 84  | 84  | 84  | 84  | 84  | 84  | 84  | 84  | 84  | 84  | 84 |  |  |  |  |  |    |  |  |  |  |  |  |  |  |
|     | 7  | 97  | 91  | 87  | 84  | 96  | 90  | 87  | 84  | 89  | 86  | 84  | 88  | 85  | 83  | 87  | 85  | 83  | 82  | 82  | 82  | 82  | 82  | 82  | 82  | 82  | 82  | 82  | 82  | 82  | 82 |  |  |  |  |  |    |  |  |  |  |  |  |  |  |
|     | 8  | 95  | 88  | 85  | 82  | 94  | 88  | 84  | 82  | 87  | 84  | 81  | 86  | 83  | 81  | 85  | 83  | 81  | 80  | 80  | 80  | 80  | 80  | 80  | 80  | 80  | 80  | 80  | 80  | 80  | 80 |  |  |  |  |  |    |  |  |  |  |  |  |  |  |
|     | 9  | 92  | 86  | 82  | 80  | 92  | 86  | 82  | 80  | 85  | 82  | 79  | 84  | 81  | 79  | 84  | 81  | 79  | 78  | 78  | 78  | 78  | 78  | 78  | 78  | 78  | 78  | 78  | 78  | 78  | 78 |  |  |  |  |  |    |  |  |  |  |  |  |  |  |
|     | 10 | 90  | 84  | 80  | 78  | 90  | 84  | 80  | 78  | 83  | 80  | 77  | 82  | 79  | 77  | 82  | 79  | 77  | 76  | 76  | 76  | 76  | 76  | 76  | 76  | 76  | 76  | 76  | 76  | 76  | 76 |  |  |  |  |  |    |  |  |  |  |  |  |  |  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |         |
|-----|---------|
|     | 0°      |
| 0°  | 2644173 |
| 5°  | 2438544 |
| 10° | 1643291 |
| 15° | 810228  |
| 20° | 346096  |
| 25° | 136037  |
| 30° | 53550   |
| 35° | 23489   |
| 40° | 11271   |
| 45° | 5442    |
| 50° | 2993    |
| 55° | 1634    |
| 60° | 987     |
| 65° | 584     |
| 70° | 721     |
| 75° | 0       |
| 80° | 0       |
| 85° | 0       |



TEST NUMBER: P314975

CATALOG NUMBER: LDA2B10NFL8040D010 PIN1MMS

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 417.1  | 40.4      |
| 10°-20°   | 449.2  | 43.5      |
| 20°-30°   | 129.7  | 12.6      |
| 30°-40°   | 27.4   | 2.6       |
| 40°-50°   | 6.7    | 0.7       |
| 50°-60°   | 1.9    | 0.2       |
| 60°-70°   | 0.7    | 0.1       |
| 70°-80°   | 0.3    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 996.0  | 96.4      |
| 0°-40°    | 1023.4 | 99.1      |
| 0°-60°    | 1032.0 | 99.9      |
| 0°-90°    | 1033.1 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1033.1 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 5360 |      |
| 5°  | 4924 | 417  |
| 15° | 1586 | 449  |
| 25° | 250  | 130  |
| 35° | 39   | 27   |
| 45° | 8    | 7    |
| 55° | 2    | 2    |
| 65° | 0    | 1    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P314975

CATALOG NUMBER: LDA2B10NFL8040D010 PIN1MMS

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 5359.5 |
| 1°    | 5325.9 |
| 2°    | 5268.9 |
| 3°    | 5191.9 |
| 4°    | 5082.8 |
| 5°    | 4923.9 |
| 6°    | 4709.6 |
| 7°    | 4429.9 |
| 8°    | 4086.0 |
| 9°    | 3685.0 |
| 10°   | 3280.2 |
| 11°   | 2871.0 |
| 12°   | 2484.6 |
| 13°   | 2141.7 |
| 14°   | 1840.1 |
| 15°   | 1586.3 |
| 17.5° | 1048.4 |
| 20°   | 659.2  |
| 22.5° | 405.3  |
| 25°   | 249.9  |
| 27.5° | 152.5  |
| 30°   | 94.0   |
| 32.5° | 59.4   |
| 35°   | 39.0   |
| 37.5° | 25.8   |
| 40°   | 17.5   |
| 42.5° | 12.2   |
| 45°   | 7.8    |
| 47.5° | 4.9    |
| 50°   | 3.9    |
| 52.5° | 2.9    |
| 55°   | 1.9    |
| 57.5° | 1.5    |
| 60°   | 1.0    |
| 62.5° | 1.0    |
| 65°   | 0.5    |
| 67.5° | 0.5    |
| 70°   | 0.5    |
| 72.5° | 0.5    |
| 75°   | 0.0    |
| 77.5° | 0.5    |
| 80°   | 0.0    |
| 82.5° | 0.0    |



TEST NUMBER: P314975

CATALOG NUMBER: LDA2B10NFL8040D010 PIN1MMS

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







|       |  |     |
|-------|--|-----|
| 85°   |  | 0.0 |
| 87.5° |  | 0.0 |



(END OF REPORT)