

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P278595

Luminaire Tested: **LDA2B108050D010 EU2B10NFL258050 2LBAD1LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P278595
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B108050D010 EU2B10NFL258050 2LBAD1LI
Description: PORTFOLIO 2IN ADJ 1000 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC AND 2in ADJ spun Refl, Self-Flanged, LI
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1184.9 lumens
Efficiency: N/A
Efficacy: 118.5 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P278595

CATALOG NUMBER: LDA2B108050D010 EU2B10NFL258050 2LBAD1LI

Luminous Intensity Polar Plot





TEST NUMBER: P278595

CATALOG NUMBER: LDA2B108050D010 EU2B10NFL258050 2LBAD1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20								
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100	100	100	100	100	100	100															
	1	115	113	111	110	113	111	109	108	107	106	105	103	102	102	100	99	99	97	97	97	97	97	97	97	97	97	97	97	97															
	2	112	108	105	103	110	107	104	102	103	101	100	101	99	98	98	97	96	94	94	94	94	94	94	94	94	94	94	94	94															
	3	108	104	100	98	107	103	99	97	100	98	95	98	96	94	96	94	93	91	91	91	91	91	91	91	91	91	91	91	91															
	4	105	100	96	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89	89	89	89	89	89	89	89	89	89	89	89															
	5	102	97	93	90	101	96	92	90	94	91	89	93	90	88	92	89	87	86	86	86	86	86	86	86	86	86	86	86	86															
	6	100	94	90	87	98	93	89	87	92	89	86	91	88	86	89	87	85	84	84	84	84	84	84	84	84	84	84	84	84	84														
	7	97	91	87	84	96	90	87	84	89	86	84	88	85	83	87	85	83	82	82	82	82	82	82	82	82	82	82	82	82	82														
	8	95	88	85	82	94	88	84	82	87	84	81	86	83	81	85	83	81	80	80	80	80	80	80	80	80	80	80	80	80	80														
	9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78	78	78	78	78	78	78	78	78	78	78	78	78														
	10	90	84	80	78	90	84	80	78	83	80	77	82	79	77	82	79	77	76	76	76	76	76	76	76	76	76	76	76	76	76														

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3032794
5°	2797003
10°	1884810
15°	929287
20°	396919
25°	156069
30°	61412
35°	26922
40°	12945
45°	6210
50°	3454
55°	1892
60°	1085
65°	700
70°	865
75°	0
80°	0
85°	0



TEST NUMBER: P278595

CATALOG NUMBER: LDA2B108050D010 EU2B10NFL258050 2LBAD1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	478.4	40.4
10°-20°	515.2	43.5
20°-30°	148.8	12.6
30°-40°	31.4	2.6
40°-50°	7.7	0.7
50°-60°	2.2	0.2
60°-70°	0.8	0.1
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1142.4	96.4
0°-40°	1173.8	99.1
0°-60°	1183.7	99.9
0°-90°	1184.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1184.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6147	
5°	5648	478
15°	1819	515
25°	287	149
35°	45	31
45°	9	8
55°	2	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P278595

CATALOG NUMBER: LDA2B108050D010 EU2B10NFL258050 2LBAD1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	6147.2
1°	6108.7
2°	6043.3
3°	5955.0
4°	5829.8
5°	5647.7
6°	5401.8
7°	5081.0
8°	4686.5
9°	4226.7
10°	3762.3
11°	3292.9
12°	2849.8
13°	2456.4
14°	2110.5
15°	1819.4
17.5°	1202.5
20°	756.0
22.5°	464.9
25°	286.7
27.5°	174.9
30°	107.8
32.5°	68.2
35°	44.7
37.5°	29.6
40°	20.1
42.5°	14.0
45°	8.9
47.5°	5.6
50°	4.5
52.5°	3.4
55°	2.2
57.5°	1.7
60°	1.1
62.5°	1.1
65°	0.6
67.5°	0.6
70°	0.6
72.5°	0.6
75°	0.0
77.5°	0.6
80°	0.0
82.5°	0.0



TEST NUMBER: P278595

CATALOG NUMBER: LDA2B108050D010 EU2B10NFL258050 2LBAD1LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)