

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P497110

Luminaire Tested: **LDA2B109730R60D010 2LBD1H**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P497110  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-53)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/8/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B109730R60D010 2LBD1H  
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 97 CRI LEDS AND 3000K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 771.9 lumens  
Efficiency: N/A  
Efficacy: 77.2 lumens/watt  
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.87  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P497110  
CATALOG NUMBER: LDA2B109730R60D010 2LBD1H

### Luminous Intensity Polar Plot





TEST NUMBER: P497110

CATALOG NUMBER: LDA2B109730R60D010 2LBD1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	108	104	100	96	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	96	91	88	93	89	86		91	87	85		88	86	84	82
4	98	91	86	81	96	90	85	81	88	83	80		86	82	79		84	81	78	77
5	93	85	80	75	92	84	79	75	83	78	74		81	77	74		79	76	73	72
6	89	80	74	70	87	79	74	70	78	73	70		77	72	69		75	72	69	67
7	85	76	70	66	83	75	69	66	74	69	65		73	68	65		71	67	64	63
8	81	71	66	62	79	71	65	61	70	65	61		69	64	61		68	64	61	59
9	77	68	62	58	76	67	62	58	66	61	58		65	61	57		64	60	57	56
10	73	64	58	55	72	64	58	54	63	58	54		62	57	54		61	57	54	53

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	462132
5°	438739
10°	429534
15°	415712
20°	380118
25°	337452
30°	252427
35°	142500
40°	53648
45°	24002
50°	11743
55°	2322
60°	789
65°	467
70°	577
75°	0
80°	0
85°	0



TEST NUMBER: P497110

CATALOG NUMBER: LDA2B109730R60D010 2LBD1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	83.9	10.9
10°-20°	226.1	29.3
20°-30°	276.2	35.8
30°-40°	150.6	19.5
40°-50°	30.1	3.9
50°-60°	4.3	0.6
60°-70°	0.5	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	586.1	75.9
0°-40°	736.8	95.4
0°-60°	771.2	99.9
0°-90°	771.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	771.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	937	
5°	886	84
15°	814	226
25°	620	276
35°	237	151
45°	34	30
55°	3	4
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P497110

CATALOG NUMBER: LDA2B109730R60D010 2LBD1H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	936.7
1°	932.4
2°	924.2
3°	913.3
4°	897.6
5°	885.9
6°	879.6
7°	872.2
8°	866.3
9°	863.6
10°	857.4
11°	850.3
12°	844.1
13°	836.6
14°	825.7
15°	813.9
16°	799.1
17°	778.3
18°	765.0
19°	743.5
20°	724.0
21°	706.0
22.5°	675.9
23°	663.4
24°	644.2
25°	619.9
26°	589.0
27°	556.6
28°	519.4
29°	484.2
30°	443.1
32.5°	339.9
35°	236.6
37.5°	148.2
40°	83.3
42.5°	52.0
45°	34.4
47.5°	23.5
50°	15.3
52.5°	7.8
55°	2.7
57.5°	1.2
60°	0.8
62.5°	0.8
65°	0.4



TEST NUMBER: P497110

CATALOG NUMBER: LDA2B109730R60D010 2LBD1H

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)