

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P278008

Luminaire Tested: **LDA2B108050D010 EU2B10SP158050 2LBAD1WHH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P278008
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-1)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B108050D010 EU2B10SP158050 2LBAD1WHH
Description: PORTFOLIO 2IN ADJ 1000 LUMEN LED LUMINAIRE WITH SPOT OPTIC AND 2in
ADJ spun Refl, Self-Flanged, WHH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1131.3 lumens
Efficiency: N/A
Efficacy: 113.1 lumens/watt
Spacing Criteria (0/90/45): 0.28 / 0.28 / 0.28
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P278008

CATALOG NUMBER: LDA2B108050D010 EU2B10SP158050 2LBAD1WHH

Luminous Intensity Polar Plot





TEST NUMBER: P278008

CATALOG NUMBER: LDA2B108050D010 EU2B10SP158050 2LBAD1WHH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	116	114	112	110	113	112	110	109	108	106	105	104	103	102	101	100	99	98		
2	112	109	107	104	110	108	105	103	105	103	101	102	100	99	99	98	97	96		
3	109	105	102	100	108	104	101	99	102	99	98	100	98	96	97	96	95	93		
4	107	102	99	96	105	101	98	96	99	97	95	98	95	94	96	94	93	92		
5	104	99	96	93	103	99	95	93	97	94	92	96	93	91	94	92	91	90		
6	102	97	93	91	101	96	93	91	95	92	90	94	91	89	93	91	89	88		
7	100	95	91	89	99	94	91	88	93	90	88	92	90	88	91	89	87	86		
8	98	93	89	87	97	92	89	87	91	88	86	90	88	86	90	87	86	85		
9	96	91	87	85	95	90	87	85	90	87	85	89	86	84	88	86	84	83		
10	94	89	86	83	94	89	85	83	88	85	83	87	85	83	87	85	83	82		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	5110488
5°	4074392
10°	1768884
15°	611131
20°	250594
25°	113173
30°	45518
35°	21200
40°	11528
45°	4256
50°	2610
55°	1892
60°	1085
65°	700
70°	865
75°	0
80°	0
85°	0



TEST NUMBER: P278008

CATALOG NUMBER: LDA2B108050D010 EU2B10SP158050 2LBAD1WHH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	621.8	55.0
10°-20°	373.4	33.0
20°-30°	102.8	9.1
30°-40°	24.4	2.2
40°-50°	6.0	0.5
50°-60°	2.0	0.2
60°-70°	0.8	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1098.0	97.1
0°-40°	1122.4	99.2
0°-60°	1130.4	99.9
0°-90°	1131.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1131.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10358	
5°	8227	622
15°	1196	373
25°	208	103
35°	35	24
45°	6	6
55°	2	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P278008

CATALOG NUMBER: LDA2B108050D010 EU2B10SP158050 2LBAD1WHH

CANDELA DISTRIBUTION (FULL):

	0°
0°	10358.5
1°	10244.0
2°	9969.6
3°	9551.0
4°	8960.2
5°	8227.0
6°	7331.7
7°	6350.9
8°	5320.4
9°	4372.5
10°	3530.9
11°	2818.3
12°	2243.3
13°	1809.0
14°	1463.7
15°	1196.5
17.5°	742.7
20°	477.3
22.5°	313.0
25°	207.9
27.5°	133.6
30°	79.9
32.5°	50.3
35°	35.2
37.5°	25.7
40°	17.9
42.5°	10.6
45°	6.1
47.5°	4.5
50°	3.4
52.5°	2.8
55°	2.2
57.5°	1.7
60°	1.1
62.5°	1.1
65°	0.6
67.5°	0.6
70°	0.6
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P278008

CATALOG NUMBER: LDA2B108050D010 EU2B10SP158050 2LBAD1WHH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)