

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P497120

Luminaire Tested: **LDA2B109730R60D010 2LBDL1H**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P497120
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-55)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B109730R60D010 2LBDL1H
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 97 CRI LEDS AND 3000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 712.1 lumens
Efficiency: N/A
Efficacy: 71.2 lumens/watt
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.86
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 10
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P497120
CATALOG NUMBER: LDA2B109730R60D010 2LBDL1H

Luminous Intensity Polar Plot





TEST NUMBER: P497120

CATALOG NUMBER: LDA2B109730R60D010 2LBDL1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82
4	98	90	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71
6	88	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67
7	84	75	69	65	83	74	69	65	73	68	65	72	68	64	71	67	64	63
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59
9	76	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55
10	73	63	58	54	72	63	58	54	62	57	54	61	57	54	61	57	53	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	421430
5°	410460
10°	399125
15°	379397
20°	346621
25°	297659
30°	221494
35°	130033
40°	61956
45°	28955
50°	14430
55°	5075
60°	1184
65°	934
70°	577
75°	762
80°	0
85°	0



TEST NUMBER: P497120

CATALOG NUMBER: LDA2B109730R60D010 2LBDL1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.0	11.0
10°-20°	206.7	29.0
20°-30°	245.4	34.5
30°-40°	138.5	19.5
40°-50°	36.0	5.1
50°-60°	6.6	0.9
60°-70°	0.7	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	530.1	74.4
0°-40°	668.6	93.9
0°-60°	711.2	99.9
0°-90°	712.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	712.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	854	
5°	829	78
15°	743	207
25°	547	245
35°	216	139
45°	42	36
55°	6	7
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P497120

CATALOG NUMBER: LDA2B109730R60D010 2LBDL1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	854.2
1°	854.6
2°	848.7
3°	843.7
4°	833.9
5°	828.8
6°	819.8
7°	813.2
8°	806.9
9°	802.6
10°	796.7
11°	785.4
12°	774.8
13°	769.0
14°	755.3
15°	742.8
16°	728.3
17°	711.1
18°	694.6
19°	675.1
20°	660.2
21°	639.9
22.5°	606.2
23°	600.4
24°	571.8
25°	546.8
26°	519.0
27°	487.0
28°	455.3
29°	424.4
30°	388.8
32.5°	299.2
35°	215.9
37.5°	147.5
40°	96.2
42.5°	63.0
45°	41.5
47.5°	28.2
50°	18.8
52.5°	11.7
55°	5.9
57.5°	2.3
60°	1.2
62.5°	0.8
65°	0.8



TEST NUMBER: P497120

CATALOG NUMBER: LDA2B109730R60D010 2LBDL1H

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.4
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)