

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P497153

Luminaire Tested: **LDA2B109730R65D010 2LBDLC1MW**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P497153
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-68)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B109730R65D010 2LBDLC1MW
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 97 CRI LEDS AND 3000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 791.9 lumens
Efficiency: N/A
Efficacy: 79.2 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.94
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 10
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P497153

CATALOG NUMBER: LDA2B109730R65D010 2LBDLC1MW

Luminous Intensity Polar Plot





TEST NUMBER: P497153

CATALOG NUMBER: LDA2B109730R65D010 2LBDLC1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	87
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80
4	97	89	83	79	95	88	83	79	86	81	78	84	80	77	82	78	76	74
5	92	83	77	73	90	82	76	72	80	75	72	79	74	71	77	73	70	69
6	87	78	72	67	85	77	71	67	75	70	66	74	69	66	73	69	65	64
7	82	73	67	62	81	72	66	62	71	66	62	70	65	61	68	64	61	60
8	78	68	62	58	77	68	62	58	67	61	58	66	61	57	65	60	57	56
9	74	64	58	54	73	64	58	54	63	58	54	62	57	54	61	57	53	52
10	71	61	55	51	70	60	54	51	59	54	50	59	54	50	58	53	50	49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	414375
5°	397089
10°	378134
15°	359375
20°	334336
25°	308655
30°	267809
35°	192128
40°	104334
45°	44584
50°	19188
55°	6881
60°	1283
65°	934
70°	577
75°	0
80°	0
85°	0



TEST NUMBER: P497153

CATALOG NUMBER: LDA2B109730R65D010 2LBDLC1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	75.1	9.5
10°-20°	197.1	24.9
20°-30°	257.7	32.5
30°-40°	196.0	24.8
40°-50°	56.7	7.2
50°-60°	8.5	1.1
60°-70°	0.7	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	529.9	66.9
0°-40°	725.9	91.7
0°-60°	791.1	99.9
0°-90°	791.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	791.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	840	
5°	802	75
15°	704	197
25°	567	258
35°	319	196
45°	64	57
55°	8	9
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P497153

CATALOG NUMBER: LDA2B109730R65D010 2LBDLC1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	839.9
1°	836.9
2°	832.2
3°	822.9
4°	812.8
5°	801.8
6°	791.2
7°	781.9
8°	773.0
9°	765.0
10°	754.8
11°	745.9
12°	736.6
13°	727.3
14°	717.2
15°	703.6
16°	693.5
17°	681.2
18°	662.6
19°	652.8
20°	636.8
21°	622.4
22.5°	600.4
23°	591.9
24°	578.8
25°	567.0
26°	551.3
27°	534.0
28°	514.9
29°	494.6
30°	470.1
32.5°	402.8
35°	319.0
37.5°	235.2
40°	162.0
42.5°	102.8
45°	63.9
47.5°	39.8
50°	25.0
52.5°	14.8
55°	8.0
57.5°	3.0
60°	1.3
62.5°	0.8
65°	0.8



TEST NUMBER: P497153

CATALOG NUMBER: LDA2B109730R65D010 2LBDLC1MW

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)