

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P280389

Luminaire Tested: **LDA2B108050D010 EU2B10WFL558050 2LBAD1B**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P280389  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-5)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA2B108050D010 EU2B10WFL558050 2LBAD1B  
Description: PORTFOLIO 2IN ADJ 1000 LUMEN LED LUMINAIRE WITH WIDE FLOOD OPTIC AND  
2in ADJ spun Refl, Self-Flanged, B  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1200.1 lumens  
Efficiency: N/A  
Efficacy: 120.0 lumens/watt  
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.73  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P280389

CATALOG NUMBER: LDA2B108050D010 EU2B10WFL558050 2LBAD1B

### Luminous Intensity Polar Plot





TEST NUMBER: P280389

CATALOG NUMBER: LDA2B108050D010 EU2B10WFL558050 2LBAD1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	109	107	112	110	108	106	106	104	103	102	101	99	98	97	97	95
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	90
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	88	86	85
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	80
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76
6	92	84	79	75	91	84	79	75	82	78	75	81	77	74	80	76	74	72
7	88	80	75	71	87	80	75	71	78	74	71	77	73	70	76	73	70	69
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	65
9	81	73	68	64	80	72	68	64	72	67	64	71	67	64	70	66	64	62
10	78	70	65	61	77	69	64	61	69	64	61	68	64	61	67	63	61	59

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1024910
5°	1004013
10°	933663
15°	815182
20°	674919
25°	516221
30°	282450
35°	104556
40°	36195
45°	16327
50°	7675
55°	3871
60°	1085
65°	700
70°	865
75°	0
80°	0
85°	0



TEST NUMBER: P280389

CATALOG NUMBER: LDA2B108050D010 EU2B10WFL558050 2LBAD1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	188.4	15.7
10°-20°	441.1	36.8
20°-30°	416.9	34.7
30°-40°	128.3	10.7
40°-50°	20.3	1.7
50°-60°	4.3	0.4
60°-70°	0.7	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1046.4	87.2
0°-40°	1174.8	97.9
0°-60°	1199.4	99.9
0°-90°	1200.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1200.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2077	
5°	2027	188
15°	1596	441
25°	948	417
35°	174	128
45°	23	20
55°	4	4
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P280389

CATALOG NUMBER: LDA2B108050D010 EU2B10WFL558050 2LBAD1B

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2077.4
1°	2069.6
2°	2060.1
3°	2052.3
4°	2042.3
5°	2027.3
6°	2007.8
7°	1981.7
8°	1946.6
9°	1906.0
10°	1863.7
11°	1816.9
12°	1767.4
13°	1713.4
14°	1657.2
15°	1596.0
17.5°	1434.1
20°	1285.5
22.5°	1134.7
25°	948.3
27.5°	723.4
30°	495.8
32.5°	304.4
35°	173.6
37.5°	96.8
40°	56.2
42.5°	35.1
45°	23.4
47.5°	15.6
50°	10.0
52.5°	6.7
55°	4.5
57.5°	2.8
60°	1.1
62.5°	0.6
65°	0.6
67.5°	0.6
70°	0.6
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P280389

CATALOG NUMBER: LDA2B108050D010 EU2B10WFL558050 2LBAD1B

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)