

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P280395

Luminaire Tested: **LDA2B108050D010 EU2B10WFL558050 2LBALD1H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P280395
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-5)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B108050D010 EU2B10WFL558050 2LBALD1H
Description: PORTFOLIO 2IN ADJ 1000 LUMEN LED LUMINAIRE WITH WIDE FLOOD OPTIC AND
2in ADJ spun Refl w/lens Self-Flanged, LI
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1189.0 lumens
Efficiency: N/A
Efficacy: 118.9 lumens/watt
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.73
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P280395

CATALOG NUMBER: LDA2B108050D010 EU2B10WFL558050 2LBALD1H

Luminous Intensity Polar Plot





TEST NUMBER: P280395

CATALOG NUMBER: LDA2B108050D010 EU2B10WFL558050 2LBALD1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	109	107	112	110	108	106	106	104	103	102	101	99	98	97	97	95			
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	90			
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	88	86	85			
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	80			
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76			
6	92	84	79	75	91	84	79	75	82	78	75	81	77	74	80	76	74	72			
7	88	80	75	71	87	80	75	71	78	74	71	77	73	70	76	73	70	69			
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	65			
9	81	73	68	64	80	72	68	64	72	67	64	71	67	64	70	66	64	62			
10	78	70	65	61	77	69	64	61	69	64	61	68	64	61	67	63	61	59			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1015388
5°	994702
10°	924996
15°	807623
20°	668671
25°	511430
30°	279829
35°	103593
40°	35873
45°	16187
50°	7599
55°	3785
60°	1085
65°	700
70°	865
75°	0
80°	0
85°	0



TEST NUMBER: P280395

CATALOG NUMBER: LDA2B108050D010 EU2B10WFL558050 2LBALD1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	186.6	15.7
10°-20°	437.0	36.8
20°-30°	413.1	34.7
30°-40°	127.2	10.7
40°-50°	20.1	1.7
50°-60°	4.3	0.4
60°-70°	0.7	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1036.7	87.2
0°-40°	1163.9	97.9
0°-60°	1188.2	99.9
0°-90°	1189.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1189.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2058	
5°	2008	187
15°	1581	437
25°	940	413
35°	172	127
45°	23	20
55°	4	4
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P280395

CATALOG NUMBER: LDA2B108050D010 EU2B10WFL558050 2LBALD1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	2058.1
1°	2050.4
2°	2041.0
3°	2033.3
4°	2023.3
5°	2008.5
6°	1989.2
7°	1963.3
8°	1928.5
9°	1888.3
10°	1846.4
11°	1800.1
12°	1751.0
13°	1697.5
14°	1641.8
15°	1581.2
17.5°	1420.8
20°	1273.6
22.5°	1124.1
25°	939.5
27.5°	716.7
30°	491.2
32.5°	301.6
35°	172.0
37.5°	95.9
40°	55.7
42.5°	34.7
45°	23.2
47.5°	15.4
50°	9.9
52.5°	6.6
55°	4.4
57.5°	2.8
60°	1.1
62.5°	0.6
65°	0.6
67.5°	0.6
70°	0.6
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P280395

CATALOG NUMBER: LDA2B108050D010 EU2B10WFL558050 2LBALD1H

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)