

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P278076

Luminaire Tested: **LDA2B10D2WD010 EU2B10SP15D2W 2LBAD1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P278076
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-1)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B10D2WD010 EU2B10SP15D2W 2LBAD1MW
Description: PORTFOLIO 2IN ADJ 1000 LUMEN LED LUMINAIRE WITH SPOT OPTIC AND 2in
ADJ spun Refl, Self-Flanged, MW
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 809.4 lumens
Efficiency: N/A
Efficacy: 80.9 lumens/watt
Spacing Criteria (0/90/45): 0.28 / 0.28 / 0.28
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P278076

CATALOG NUMBER: LDA2B10D2WD010 EU2B10SP15D2W 2LBAD1MW

Luminous Intensity Polar Plot





TEST NUMBER: P278076

CATALOG NUMBER: LDA2B10D2WD010 EU2B10SP15D2W 2LBAD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	116	114	112	110	113	112	110	109	108	106	105	104	103	102	101	100	99	98			98
2	112	109	107	104	110	108	105	103	105	103	101	102	100	99	99	98	97	96			96
3	109	105	102	100	108	104	101	99	102	99	98	100	98	96	97	96	95	93			93
4	107	102	99	96	105	101	98	96	99	97	95	98	95	94	96	94	93	92			92
5	104	99	96	93	103	99	95	93	97	94	92	96	93	91	94	92	91	90			90
6	102	97	93	91	101	96	93	91	95	92	90	94	91	89	93	91	89	88			88
7	100	95	91	89	99	94	91	88	93	90	88	92	90	88	91	89	87	86			86
8	98	93	89	87	97	92	89	87	91	88	86	90	88	86	90	87	86	85			85
9	96	91	87	85	95	90	87	85	90	87	85	89	86	84	88	86	84	83			83
10	94	89	86	83	94	89	85	83	88	85	83	87	85	83	87	85	83	82			82

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3656650
5°	2915317
10°	1265657
15°	437267
20°	179296
25°	81001
30°	32586
35°	15178
40°	8244
45°	3070
50°	1842
55°	1376
60°	789
65°	467
70°	577
75°	0
80°	0
85°	0



TEST NUMBER: P278076

CATALOG NUMBER: LDA2B10D2WD010 EU2B10SP15D2W 2LBAD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	444.9	55.0
10°-20°	267.2	33.0
20°-30°	73.6	9.1
30°-40°	17.5	2.2
40°-50°	4.3	0.5
50°-60°	1.4	0.2
60°-70°	0.5	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	785.6	97.1
0°-40°	803.1	99.2
0°-60°	808.8	99.9
0°-90°	809.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	809.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7412	
5°	5887	445
15°	856	267
25°	149	74
35°	25	17
45°	4	4
55°	2	1
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P278076

CATALOG NUMBER: LDA2B10D2WD010 EU2B10SP15D2W 2LBAD1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	7411.7
1°	7329.7
2°	7133.4
3°	6833.9
4°	6411.2
5°	5886.6
6°	5246.0
7°	4544.2
8°	3806.8
9°	3128.6
10°	2526.4
11°	2016.6
12°	1605.1
13°	1294.4
14°	1047.3
15°	856.1
17.5°	531.4
20°	341.5
22.5°	223.9
25°	148.8
27.5°	95.6
30°	57.2
32.5°	36.0
35°	25.2
37.5°	18.4
40°	12.8
42.5°	7.6
45°	4.4
47.5°	3.2
50°	2.4
52.5°	2.0
55°	1.6
57.5°	1.2
60°	0.8
62.5°	0.8
65°	0.4
67.5°	0.4
70°	0.4
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P278076

CATALOG NUMBER: LDA2B10D2WD010 EU2B10SP15D2W 2LBAD1MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)