

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P495386

Luminaire Tested: **LDA2B108050R60D010 2LBD1MW**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P495386
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-53)
Test Lab: INNOVATION CENTER
Issue Date: 3/8/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B108050R60D010 2LBD1MW
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 5000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1090.2 lumens
Efficiency: N/A
Efficacy: 109.0 lumens/watt
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.87
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 10
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P495386

CATALOG NUMBER: LDA2B108050R60D010 2LBD1MW

Luminous Intensity Polar Plot





TEST NUMBER: P495386

CATALOG NUMBER: LDA2B108050R60D010 2LBD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88
3	103	97	92	88	101	96	91	88	93	89	86	91	87	85	88	86	84	82
4	98	91	86	81	96	90	85	81	88	83	80	86	82	79	84	81	78	77
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72
6	89	80	74	70	87	79	74	70	78	73	70	77	72	69	75	72	69	67
7	85	76	70	66	83	75	69	66	74	69	65	73	68	65	71	67	64	63
8	81	71	66	62	79	71	65	61	70	65	61	69	64	61	68	64	61	59
9	77	68	62	58	76	67	62	58	66	61	58	65	61	57	64	60	57	56
10	73	64	58	55	72	64	58	54	63	58	54	62	57	54	61	57	54	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	652668
5°	619603
10°	606578
15°	587125
20°	536785
25°	476591
30°	356509
35°	201283
40°	75803
45°	33909
50°	16502
55°	3355
60°	1085
65°	700
70°	865
75°	0
80°	0
85°	0



TEST NUMBER: P495386

CATALOG NUMBER: LDA2B108050R60D010 2LBD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	118.5	10.9
10°-20°	319.3	29.3
20°-30°	390.1	35.8
30°-40°	212.7	19.5
40°-50°	42.6	3.9
50°-60°	6.1	0.6
60°-70°	0.8	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	827.8	75.9
0°-40°	1040.5	95.4
0°-60°	1089.2	99.9
0°-90°	1090.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1090.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1323	
5°	1251	118
15°	1150	319
25°	876	390
35°	334	213
45°	49	43
55°	4	6
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P495386

CATALOG NUMBER: LDA2B108050R60D010 2LBD1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1322.9
1°	1316.8
2°	1305.2
3°	1289.8
4°	1267.7
5°	1251.1
6°	1242.3
7°	1231.8
8°	1223.5
9°	1219.6
10°	1210.8
11°	1200.8
12°	1192.0
13°	1181.5
14°	1166.0
15°	1149.5
16°	1128.5
17°	1099.2
18°	1080.4
19°	1050.1
20°	1022.4
21°	997.0
22.5°	954.5
23°	936.8
24°	909.8
25°	875.5
26°	831.9
27°	786.0
28°	733.5
29°	683.8
30°	625.8
32.5°	480.0
35°	334.2
37.5°	209.3
40°	117.7
42.5°	73.5
45°	48.6
47.5°	33.1
50°	21.5
52.5°	11.0
55°	3.9
57.5°	1.7
60°	1.1
62.5°	1.1
65°	0.6



TEST NUMBER: P495386

CATALOG NUMBER: LDA2B108050R60D010 2LBD1MW

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.6
70°	0.6
72.5°	0.6
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)