

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P315034

Luminaire Tested: **LDA2B10NFLD2WD010 PINW1MW**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P315034  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA2B10NFLD2WD010 PINW1MW  
Description: PORTFOLIO 2IN ADJ 1000 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC AND 2in Adj PinHole, Black oculus, matte white finish  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 742.4 lumens  
Efficiency: N/A  
Efficacy: 74.2 lumens/watt  
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P315034

CATALOG NUMBER: LDA2B10NFLD2WD010 PINW1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P315034

CATALOG NUMBER: LDA2B10NFLD2WD010 PINW1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	113	111	110	113	111	109	108	107	106	105	103	102	102	100	99	99	97	97	97	97
2	112	108	105	103	110	107	104	102	103	101	100	101	99	98	98	97	96	94	94	94	94
3	108	104	100	98	107	103	99	97	100	98	95	98	96	94	96	94	93	91	91	91	91
4	105	100	96	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89	89	89	89
5	102	97	93	90	101	96	92	90	94	91	89	93	90	88	92	89	87	86	86	86	86
6	100	94	90	87	98	93	89	87	92	89	86	91	88	86	89	87	85	84	84	84	84
7	97	91	87	84	96	90	87	84	89	86	84	88	85	83	87	85	83	82	82	82	82
8	95	88	85	82	94	88	84	82	87	84	81	86	83	81	85	83	81	80	80	80	80
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78	78	78	78
10	90	84	80	78	90	84	80	78	83	80	77	82	79	77	82	79	77	76	76	76	76

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1899986
5°	1752231
10°	1180793
15°	582171
20°	248652
25°	97768
30°	38511
35°	16864
40°	8115
45°	3907
50°	2149
55°	1204
60°	691
65°	467
70°	577
75°	0
80°	0
85°	0



TEST NUMBER: P315034

CATALOG NUMBER: LDA2B10NFLD2WD010 PINW1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	299.7	40.4
10°-20°	322.8	43.5
20°-30°	93.2	12.6
30°-40°	19.7	2.7
40°-50°	4.8	0.7
50°-60°	1.4	0.2
60°-70°	0.5	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	715.7	96.4
0°-40°	735.4	99.1
0°-60°	741.6	99.9
0°-90°	742.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	742.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3851	
5°	3538	300
15°	1140	323
25°	180	93
35°	28	20
45°	6	5
55°	1	1
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P315034

CATALOG NUMBER: LDA2B10NFLD2WD010 PINW1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3851.1
1°	3826.9
2°	3786.0
3°	3730.7
4°	3652.2
5°	3538.1
6°	3384.1
7°	3183.1
8°	2936.0
9°	2647.9
10°	2357.0
11°	2062.9
12°	1785.3
13°	1538.9
14°	1322.2
15°	1139.8
17.5°	753.3
20°	473.6
22.5°	291.3
25°	179.6
27.5°	109.6
30°	67.6
32.5°	42.7
35°	28.0
37.5°	18.6
40°	12.6
42.5°	8.8
45°	5.6
47.5°	3.5
50°	2.8
52.5°	2.1
55°	1.4
57.5°	1.1
60°	0.7
62.5°	0.7
65°	0.4
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.0
77.5°	0.4
80°	0.0
82.5°	0.0



TEST NUMBER: P315034

CATALOG NUMBER: LDA2B10NFLD2WD010 PINW1MW

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)