

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P315705

Luminaire Tested: **LDA2B10WFLD2WD010 PIN1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P315705
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1809-951-61)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B10WFLD2WD010 PIN1MW
Description: PORTFOLIO 2IN ADJ 1000 LUMEN LED LUMINAIRE WITH WIDE FLOOD OPTIC AND
2in Adj PinHole, Black oculus, matte white finish
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 672.3 lumens
Efficiency: N/A
Efficacy: 67.2 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.68
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P315705

CATALOG NUMBER: LDA2B10WFLD2WD010 PIN1MW

Luminous Intensity Polar Plot





TEST NUMBER: P315705

CATALOG NUMBER: LDA2B10WFLD2WD010 PIN1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94																			
2	109	104	101	98	107	103	99	96	100	97	94	97	94	92	94	92	90	89																			
3	104	98	94	90	102	97	93	89	94	91	88	92	89	87	90	87	85	84																			
4	100	93	88	84	98	92	87	83	90	86	82	88	84	81	86	83	81	79																			
5	95	88	82	79	94	87	82	78	85	81	78	84	80	77	82	79	76	75																			
6	91	83	78	74	90	82	77	74	81	77	73	80	76	73	78	75	72	71																			
7	87	79	74	70	86	78	73	70	77	73	69	76	72	69	75	71	69	67																			
8	84	75	70	66	83	75	70	66	74	69	66	73	69	66	72	68	65	64																			
9	81	72	67	63	80	71	66	63	71	66	63	70	66	63	69	65	62	61																			
10	77	69	64	60	76	68	63	60	68	63	60	67	63	60	66	62	60	58																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	611522	611522	611522
5°	593157	594593	591918
10°	542954	540800	537544
15°	456676	460915	455961
20°	349246	358539	348669
25°	221774	250027	226075
30°	128977	145612	131255
35°	68178	72515	68419
40°	36002	37612	36002
45°	20094	20862	20373
50°	9441	11897	9441
55°	3441	6537	3699
60°	3947	3947	3947
65°	4203	4670	4203
70°	5193	4616	5193
75°	4766	4766	4766
80°	5114	3978	5114
85°	3962	3962	3962



TEST NUMBER: P315705

CATALOG NUMBER: LDA2B10WFLD2WD010 PIN1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	110.6	16.5
10°-20°	246.4	36.6
20°-30°	199.0	29.6
30°-40°	78.6	11.7
40°-50°	24.1	3.6
50°-60°	6.2	0.9
60°-70°	3.8	0.6
70°-80°	2.8	0.4
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	556.0	82.7
0°-40°	634.6	94.4
0°-60°	665.0	98.9
0°-90°	672.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	672.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1240	1240	1240	1240	1240	
5°	1198	1200	1201	1198	1195	111
15°	894	897	902	899	893	246
25°	407	427	459	435	415	190
35°	113	116	120	117	114	76
45°	29	29	30	30	29	24
55°	4	5	8	5	4	5
65°	4	4	4	4	4	4
75°	2	2	2	2	2	3
85°	1	1	1	1	1	1
90°	0	0	0	0	0	



TEST NUMBER: P315705

CATALOG NUMBER: LDA2B10WFLD2WD010 PIN1MW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1239.5	1239.5	1239.5	1239.5	1239.5
2.5°	1224.0	1224.8	1225.8	1224.4	1220.8
5°	1197.7	1199.9	1200.6	1198.1	1195.2
7.5°	1154.5	1151.9	1154.1	1149.8	1146.2
10°	1083.8	1080.5	1079.5	1073.0	1073.0
12.5°	996.5	995.5	996.2	992.9	987.9
15°	894.1	896.7	902.4	898.8	892.7
17.5°	785.6	789.2	794.3	793.2	784.9
20°	665.2	675.7	682.9	676.0	664.1
22.5°	528.2	550.5	568.9	554.5	535.0
25°	407.4	426.9	459.3	434.8	415.3
27.5°	309.0	323.0	352.6	328.5	315.1
30°	226.4	235.1	255.6	239.8	230.4
32.5°	161.9	168.0	176.7	167.3	162.6
35°	113.2	116.5	120.4	116.8	113.6
37.5°	79.7	80.8	83.6	80.8	79.3
40°	55.9	56.2	58.4	56.6	55.9
42.5°	40.4	40.4	41.5	40.7	40.4
45°	28.8	29.2	29.9	29.6	29.2
47.5°	20.6	21.3	21.3	21.6	20.2
50°	12.3	15.1	15.5	15.1	12.3
52.5°	6.5	9.0	11.2	9.0	6.5
55°	4.0	5.4	7.6	5.4	4.3
57.5°	4.0	4.0	5.0	4.3	4.0
60°	4.0	4.0	4.0	4.0	4.0
62.5°	4.0	4.0	4.0	4.0	4.0
65°	3.6	4.0	4.0	4.0	3.6
67.5°	3.6	3.6	3.6	3.6	3.6
70°	3.6	3.6	3.2	3.6	3.6
72.5°	3.2	3.2	2.9	3.2	3.2
75°	2.5	2.5	2.5	2.5	2.5
77.5°	2.2	2.2	2.2	2.2	2.2
80°	1.8	1.8	1.4	1.8	1.8
82.5°	1.1	1.1	1.1	1.1	1.1
85°	0.7	0.7	0.7	0.7	0.7
87.5°	0.4	0.4	0.4	0.4	0.4
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180° - - 45°-225° - - - - 90°-270°







(END OF REPORT)