

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P314981

Luminaire Tested: **LDA2B10NFL8050D010 PIN1MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P314981
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B10NFL8050D010 PIN1MMS
Description: PORTFOLIO 2IN ADJ 1000 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC
AND 2in Adj PinHole, Black oculus, matte metallic silver finish
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1026.3 lumens
Efficiency: N/A
Efficacy: 102.6 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P314981

CATALOG NUMBER: LDA2B10NFL8050D010 PIN1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P314981

CATALOG NUMBER: LDA2B10NFL8050D010 PIN1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	115	113	111	110	113	111	109	108	107	106	105	103	102	102	100	99	99	97				97															
2	112	108	105	103	110	107	104	102	103	101	100	101	99	98	98	97	96	94				94															
3	108	104	100	98	107	103	99	97	100	98	95	98	96	94	96	94	93	91				91															
4	105	100	96	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89				89															
5	102	97	93	90	101	96	92	90	94	91	89	93	90	88	92	89	87	86				86															
6	100	94	90	87	98	93	89	87	92	89	86	91	88	86	89	87	85	84				84															
7	97	91	87	84	96	90	87	84	89	86	84	88	85	83	87	85	83	82				82															
8	95	88	85	82	94	88	84	82	87	84	81	86	83	81	85	83	81	80				80															
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78				78															
10	90	84	80	78	90	84	80	78	83	80	77	82	79	77	82	79	77	76				76															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2626905
5°	2422646
10°	1632570
15°	804916
20°	343839
25°	135166
30°	53209
35°	23308
40°	11206
45°	5372
50°	2993
55°	1634
60°	987
65°	584
70°	721
75°	0
80°	0
85°	0



TEST NUMBER: P314981

CATALOG NUMBER: LDA2B10NFL8050D010 PIN1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	414.4	40.4
10°-20°	446.3	43.5
20°-30°	128.9	12.6
30°-40°	27.2	2.6
40°-50°	6.7	0.7
50°-60°	1.9	0.2
60°-70°	0.7	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	989.5	96.4
0°-40°	1016.7	99.1
0°-60°	1025.3	99.9
0°-90°	1026.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1026.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5324	
5°	4892	414
15°	1576	446
25°	248	129
35°	39	27
45°	8	7
55°	2	2
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P314981

CATALOG NUMBER: LDA2B10NFL8050D010 PIN1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	5324.5
1°	5291.1
2°	5234.5
3°	5158.0
4°	5049.6
5°	4891.8
6°	4678.9
7°	4401.1
8°	4059.4
9°	3661.0
10°	3258.8
11°	2852.2
12°	2468.4
13°	2127.7
14°	1828.1
15°	1575.9
17.5°	1041.6
20°	654.9
22.5°	402.7
25°	248.3
27.5°	151.5
30°	93.4
32.5°	59.0
35°	38.7
37.5°	25.7
40°	17.4
42.5°	12.1
45°	7.7
47.5°	4.8
50°	3.9
52.5°	2.9
55°	1.9
57.5°	1.5
60°	1.0
62.5°	1.0
65°	0.5
67.5°	0.5
70°	0.5
72.5°	0.5
75°	0.0
77.5°	0.5
80°	0.0
82.5°	0.0



TEST NUMBER: P314981

CATALOG NUMBER: LDA2B10NFL8050D010 PIN1MMS

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)